

UNITRONIC® BUS PB ROBUST

PROFIBUS -

PROFIBUS-DP, -FMS FIP , , tensides, , UV() , .
-40 ° C ~ + 80 ° C

(Weather Resistance)

Good chemical resistance please see Appendix T1



Lapp



PROFIBUS

PROFIBUS-DP FIP

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® BUS PB ROBUST

UV-

: IEC 60332-1-2

PNO

(A, PROFIBUS-DP):

93.75 kbit/s = 1200 m

187.5 kbit/s = 1000 m

500 kbit/s = 400 m

1.5 Mbit/s = 200 m

12.0 Mbit/s = 100 m

() : , O2Y(S)

:

: TPE, (RAL 4001)

,

()

TPE

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

:

(1 kHz): approx. 28.5 nF/km

:

() 250 V

:

: 75 mm

:

/ : 1500 V

/ : 1500 V

::

(3 - 20 MHz): 150 ± 15 Ohm

:

-40°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

SIMATIC® SIEMENS AG

. FIP World FIP

Lapp Kabel PROFIBUS user organisation (PNO)

가 VAT

가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® BUS PB ROBUST

		() x () x (mm)	(mm)	(kg/km)	(kg/km)
2170620	UNITRONIC® BUS PB ROBUST	1 x 2 x 0.64	8	26	55

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16