

# UNITRONIC® BUS PB 105 plus

+105°C 가 PROFIBUS , +120°C 가  
 PROFIBUS-DP, -FMS FIP , 가 가 . -40°C bis +105°C  
 ( : +120°C)



Lapp



-



가

105°C, 120°C

DIN 19245 EN 50170 . ) SIEMENS SIMATIC NET FIP ( )

7-가 ,  
 : (PP)  
 : TPE, (RAL 4001)

(07.05.2024)

# UNITRONIC® BUS PB 105 plus

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	(800 Hz): max. 30 nF/km
:	( ) 250 V
:	: 45 mm (1 )
	: 65 mm
:	/ : 1500 V
	Core/screen: 1500 V eff.
..	(3 - 20 MHz): 150 ± 15 Ohm
:	: -40°C to +105°C
	- : +120 °C

가 VAT 가 가 .



# UNITRONIC® BUS PB 105 plus

		( ) x ( ) x (mm)	(mm)	(kg/km)
2170635	UNITRONIC® BUS PB 105 plus	1x2x0,64	8	30.1

(07.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16