

# Coaxial - RG

-55 ° C + 250



가

(24.04.2024)

# Coaxial - RG

ETIM 5:

ETIM 5.0 Class-ID: EC000019

ETIM 5.0 Class-Description: Koaxialkabel

ETIM 6:

ETIM 6.0 Class-ID: EC000019

ETIM 6.0 Class :

:

- (PE) 2.3

- , (PE-ho) 1.5

- (PTFE) 2.1

:

: 6 x

:

MIL-DTL17 H

:

: PE :

-40°C +80°C

: PVC :

-40°C +80°C

:

-55°C +250°C

가 가 . ( . ) 가 .  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

가 VAT 가 가 .

		Character istic impe dance in ohm	Capacity pF/m	(%)	50 Hz eff. kV	(kV)		Ø (mm)		Ø			(mm)	(kg/km)	(kg/km)
: 50 ohm															
2170000	RG-58 C/U	50 +/- 2	101	66	2	5	CuLivz	0.9	PE	2.95	Cvz	PVC	4.95	19.1	38
2170001	RG-174 A/U	50 +/- 2	101	66	1.5	2	StCuLibl	0.48	PE	1.52	Cvz	PVC	2.8	5.4	12
2170002	RG-178 B/U	50 +/- 2	95	70	0.7	2	StCuLivs	0.3	PTFE	0.86	Cvs	FEP	1.91	4.4	9
2170003	RG-188 A/U	50 +/- 2	95	70	1.5	2	StCuLivs	0.51	PTFE	1.52	Cvs	PTFE	2.76	8.3	17.5
2170005	RG-213 /U	50 +/- 2	101	66	5	10	CuLibl	2.25	PE	7.25	Cbl	PVC	10.3	75.8	157
2170006	RG-214 /U	50 +/- 2	101	66	5	10	CuLivs	2.25	PE	7.25	CvsCvs	PVC	10.8	117.8	207
2170007	RG-223 /U	50 +/- 2	101	66	2	3	CuMvs	0.89	PE	2.95	CvsCvs	PVC	5.5	38.5	60
: 75 ohm															
2170016	RG-6 A/U	75 +/- 3	67	66	2	5	StCuMbl	0.72	PE	4.7	Cbl	PVC	8.4	72	120
2170009	RG-11 A/U	75 +/- 3	67	66	5	10	CuLivz	1.2	PE	7.3	Cbl	PVC	10.3	55.5	140
2170011	RG-11 A/U outdoor	75 +/- 3	67	66	5	10	CuLivz	1.2	PE	7.3	Cbl	PVC	12.1	55.5	170
2170012	RG-59 B/U	75 +/- 3	67	66	1.7	7	StCuMbl	0.6	PE	3.7	Cbl	PVC	6.15	25	57
2170010	RG-187 A/U	75 +/- 3	65	70	1.5	2	StCuLivs	0.31	PTFE	1.52	Cvs	PTFE	2.8	7.3	17
: 100 Ohm															
2170008	RG-62 A/U	93 +/- 5	43	75	0.8	2	StCuMbl	0.65	PE	3.7	Cbl	PVC	6.15	26	52

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## Coaxial - RG



(24.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## Coaxial - RG



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16