



UNITRONIC® RE-2Y(ST)Yv PiMF

RE-2Y (ST) Yv PiMF: PVC , 7 , PiMF/ , / , PVC

CPR: www.lappkabel.com/cpr



- (TP) (Crosstalk)

가

가

1.8 mm

: IEC 60332-1-2

EN 50288-7

7

PE()

가

PiMF

1 가 (),
가
(Drain Wire)

PVC

: (RAL 9005)

(23.04.2024)

UNITRONIC® RE-2Y(ST)Yv PiMF

(RAL 5015)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	a- : ; b- : :
:	1-1, 2-2, 3-3, 4-4 etc. (at 800 Hz max): C/C: 0.5 mm ² : 75 nF/km
:	(at 800 Hz max): C/C: 1.3 mm ² : 100 nF/km
:	. 0.75 mH/km
:	0.5 mm ² : . 39.2 ohm/km
:	1.3 mm ² : . 14.2 ohm/km
:	: 15 x : 7.5 x
- :	At 60 kHz: min. 1.02 dB/km
:	Core/core: 2000 V Core/screen: 600 V
∴	100 ohms
:	Occasional flexing: -5°C ~ +50°C : -40°C +80°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

UNITRONIC® RE-2Y(ST)Yv PiMF

	(mm ²)	(mm)	[kg/km]	[kg/km]
RE-2Y(ST)Yv PiMF 0.5 mm ²				
0032438	2.0 x 2.0 x 0.5	10.5	35	128
0032442	12.0 x 2.0 x 0.5	16.9	161	325
0.5 mm ²				
0032448	2.0 x 2.0 x 0.5	10.5	35	128
0032449	4.0 x 2.0 x 0.5	11.6	60	170
0032450	8.0 x 2.0 x 0.5	14.6	121	261
0032451	10.0 x 2.0 x 0.5	16.5	136	285
0032453	16.0 x 2.0 x 0.5	19.1	212	430
1.3 mm ²				
0032458	2.0 x 2.0 x 1.3	12.4	68	184
1.3 mm ²				
0032464	2.0 x 2.0 x 1.3	12.4	68	184
0032465	4.0 x 2.0 x 1.3	14.2	124	269
0032466	8.0 x 2.0 x 1.3	17.7	239	442
0032467	12.0 x 2.0 x 1.3	22	353	593

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16