

UNITRONIC® LiYCY (TP)

DIN 47100 , 가

UNITRONIC® LiYCY (TP): PVC , DIN 47100 , 0.34² Maxi TERMI-POINT®, , ,

TP = 가 가
CPR: www.lappkabel.com/cpr



- (TP) (Crosstalk)

() , , .

: IEC 60332-1-2 , (,)

VDE 0812

PVC 가

UNITRONIC® LiYCY (TP)

TP

Outer sheath made of PVC

Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	DIN 47100, T9
:	C/C: 120nF/km C/S: 160nF/km
:	0.65 mH/km
:	: 15 x
:	: 6 x
:	: -5°C ~ +70°C
:	: -40°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

	(mm ²)	(mm)	[kg/km]	[kg/km]
UNITRONIC® LIYCY (TP)				
0035131	2 x 2 x 0.14	5.3	18.5	39
0035141	3 x 2 x 0.14	5.8	23	48
0035132	4 x 2 x 0.14	6.2	26.6	54
0035133	6 x 2 x 0.14	7.1	48.5	85
0035150	8 x 2 x 0.14	8.2	53.7	97
0035134	10 x 2 x 0.14	8.7	59	110
0035135	12 x 2 x 0.14	8.9	66	142
0035136	16 x 2 x 0.14	10.2	79	154
0035142	20 x 2 x 0.14	11.3	97	184
0035137	25 x 2 x 0.14	12.5	113	238
0035800	2 x 2 x 0.25	6.3	28	54
0035801	3 x 2 x 0.25	7.1	39.6	68.5
0035802	4 x 2 x 0.25	7.6	44.9	81
0035803	6 x 2 x 0.25	8.5	69.5	115
0035804	8 x 2 x 0.25	10.3	76.9	130
0035805	10 x 2 x 0.25	11	102	158
0035806	12 x 2 x 0.25	11.3	120	190
0035807	16 x 2 x 0.25	12.5	146.5	238
0035808	25 x 2 x 0.25	16.1	205	344
0035810	2 x 2 x 0.5	7.9	48.1	93
0035811	3 x 2 x 0.5	8.7	73.7	116
0035812	4 x 2 x 0.5	9.4	82	127
0035813	6 x 2 x 0.5	11.1	110	198
0035814	8 x 2 x 0.5	13.1	139	259
0035816	12 x 2 x 0.5	14.9	198.3	354
0035817	16 x 2 x 0.5	16.5	240	459
0035820	2 x 2 x 0.75	8.5	58	106
0035821	3 x 2 x 0.75	9.4	84	140
0035822	4 x 2 x 0.75	10.7	108	179
0035827	5 x 2 x 0.75	11.1	126	215
0035823	6 x 2 x 0.75	12.1	146	246
0035824	8 x 2 x 0.75	14.7	180	305
0035825	12 x 2 x 0.75	16.2	261	456

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® LIYCY (TP)

	(mm ²)	(mm)	[kg/km]	[kg/km]
0035830	2 x 2 x 1.0	9	84	142
0035831	3 x 2 x 1.0	10	96	173
0035832	4 x 2 x 1.0	11.3	121	212
0035836	5 x 2 x 1.0	11.8	161	266

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16