



UNITRONIC® LiYY

DIN 47100

UNITRONIC® LiYY: PVC DIN47100 (0.34mm² Maxi TERMINAL-POINT®),

가 가
CPR: www.lappkabel.com/cpr



가 가

UNITRONIC® LiYY, ,
가

가 가, LiYY 가
: IEC 60332-1-2

VDE 0812

/ 가 (0.34 mm²)

PVC

(24.04.2024)
©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet
PN 0456 / 02_03.16

UNITRONIC® LiYY

Outer sheath made of PVC

Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:

ETIM 5.0 Class-ID: EC000104

ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104

ETIM 6.0 Class :

:

DIN 47100 , T9

:

120 nF/km

:

0.65 mH/km

:

0.34mm²: 7

:

: 10 x

: 4 x

:

: -5°C ~ +70°C

: -40°C +80°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: ≤ 30 kg or ≤ 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® LIYY

	(CORE) / (mm ²)	(mm)	[kg/km]	[kg/km]
UNITRONIC® LIYY				
0028202	2 x 0.14	3.2	2.7	13.2
0028203	3 x 0.14	3.4	4.05	16
0028204	4 x 0.14	3.6	5.4	18.9
0028205	5 x 0.14	3.9	6.72	22.2
0028207	7 x 0.14	4.2	9.45	28.4
0028208	8 x 0.14	4.9	10.2	35.2
0028210	10 x 0.14	5.2	13.5	41.2
0028212	12 x 0.14	5.6	16.2	48.4
0028214	14 x 0.14	5.8	18.9	52.9
0028216	16 x 0.14	6.1	21.6	59.1
0028220	20 x 0.14	7	27	70.8
0028225	25 x 0.14	7.8	33.6	87.2
0028236	36 x 0.14	8.6	48.6	126.8
0028237	37 x 0.14	8.9	49.7	118
0028240	40 x 0.14	9.3	54	139.1
0028250	50 x 0.14	10.4	67.5	170.9
0028256	56 x 0.14	10.7	78.4	187
0028302	2 x 0.25	3.8	4.8	18
0028303	3 x 0.25	4	7.2	22
0028304	4 x 0.25	4.3	9.6	26.2
0028305	5 x 0.25	4.7	12	31
0028306	6 x 0.25	5.1	14.4	39
0028307	7 x 0.25	5.1	16.8	42
0028308	8 x 0.25	6.2	19.2	49.2
0028310	10 x 0.25	6.8	24	58
0028312	12 x 0.25	7	28.8	67
0028314	14 x 0.25	7.3	33.6	75.3
0028316	16 x 0.25	7.7	38.4	84.3
0028318	18 x 0.25	8.1	43.2	93
0028320	20 x 0.25	8.6	48	102
0028325	25 x 0.25	9.6	60	134
0028330	30 x 0.25	10.3	72	155
0028332	32 x 0.25	10.7	76.8	164

	(CORE) / (mm ²)	(mm)	[kg/km]	[kg/km]
0028336	36 x 0.25	11.1	86.4	182.2
0028337	37 x 0.25	11.4	88.8	185
0028340	40 x 0.25	12	96.1	200
0028350	50 x 0.25	12.9	120	257.1
0028402	2 x 0.34	4.2	6.6	25
0028403	3 x 0.34	4.4	9.9	31
0028404	4 x 0.34	4.8	13.1	43.2
0028405	5 x 0.34	5.5	16.5	53.8
0028406	6 x 0.34	5.9	19.6	55
0028407	7 x 0.34	5.9	22.8	62
0028408	8 x 0.34	7.1	26.1	73.1
0028410	10 x 0.34	7.6	32.6	82
0028412	12 x 0.34	7.8	39.1	102
0028414	14 x 0.34	8.2	45.7	109
0028416	16 x 0.34	8.7	52	127
0028420	20 x 0.34	9.6	65.2	159.3
0028421	21 x 0.34	10.4	68.6	167
0028425	25 x 0.34	11.2	81.6	190
0028430	30 x 0.34	11.6	98	226
0028436	36 x 0.34	12.5	118	284
0028440	40 x 0.34	13.5	131	317
0028450	50 x 0.34	15	163	407
0028502	2 x 0.5	4.7	9.6	30
0028503	3 x 0.5	5	14.4	39
0028504	4 x 0.5	5.6	19.2	49
0028505	5 x 0.5	6.1	24	65
0028507	7 x 0.5	6.9	33.6	82
0028508	8 x 0.5	8	38.4	90
0028510	10 x 0.5	8.6	48	117
0028512	12 x 0.5	8.9	58	133
0028516	16 x 0.5	10.2	77	170
0028520	20 x 0.5	11.4	96	214
0028525	25 x 0.5	12.7	120	265
0028530	30 x 0.5	13.2	144	304

	(CORE) / (mm ²)	(mm)	[kg/km]	[kg/km]
0028540	40 x 0.5	15.8	192	392
0028602	2 x 0.75	5.1	14.4	48
0028603	3 x 0.75	5.6	21.6	57
0028604	4 x 0.75	6.1	28.8	69
0028605	5 x 0.75	6.9	36	78
0028607	7 x 0.75	7.5	50	112
0028608	8 x 0.75	8.7	58	126
0028610	10 x 0.75	9.4	72	149
0028612	12 x 0.75	10.1	86	176
0028616	16 x 0.75	11.2	115	218
0028620	20 x 0.75	12.4	144	274
0028625	25 x 0.75	14	180	320
0028702	2 x 1.0	5.6	19.2	55
0028703	3 x 1.0	5.9	29	70
0028704	4 x 1.0	6.4	38.4	79
0028705	5 x 1.0	7.3	48	98
0028802	2 x 1.5	6.2	29	74
0028803	3 x 1.5	6.8	43	89
0028804	4 x 1.5	7.4	58	105

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16