

UNITRONIC® LiHCH (TP)

DIN 47100 , 가

UNITRONIC® LiHCH (TP): (0.34 mm² Maxi TERMINAL-POINT®) 47100

TP =
CPR: www.lappkabel.com/cpr



: 가

- (TP) (Crosstalk)

가 가

: IEC 60332-1-2

(LSZH)

IEC 60754-1 , IEC 60754-2 가 / , . EN 50305 가
IEC 61034-2

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® LIHCH (TP)

VDE 0812

가

TP

: (RAL 7032)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

DIN 47100 , T9

:

C/C approx. 80 nF/km
C/S approx. 120 nF/km

:

At 1 kHz: approx. 300 pF/100 m

:

0.65 mH/km

:

:

: 15 x

: 6 x

:

1200 V

:

: -5°C ~ +70°C

: -30°C +80°C

가 가 () 가

: www.lappkabel.de/en/cable-standradlengths

30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가

(24.04.2024)



UNITRONIC® LIHCH (TP)

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
UNITRONIC® LIHCH (TP)				
0038302	2 x 2 x 0.14	5.5	18.5	39
0038303	3 x 2 x 0.14	6	23	48
0038304	4 x 2 x 0.14	6.4	26.6	54
0038308	8 x 2 x 0.14	8.4	53.7	97
0038312	12 x 2 x 0.14	9.1	66	142
0038316	16 x 2 x 0.14	10.4	79	154
0038325	25 x 2 x 0.14	12.7	113	238
0038402	2 x 2 x 0.25	6.5	28	54
0038403	3 x 2 x 0.25	7.3	39.6	66
0038404	4 x 2 x 0.25	7.8	44.9	81
0038406	6 x 2 x 0.25	8.7	69.5	115
0038408	8 x 2 x 0.25	10.5	76.9	130
0038412	12 x 2 x 0.25	11.5	120	190
0038416	16 x 2 x 0.25	12.7	146.5	238
0038602	2 x 2 x 0.5	8.1	48.1	93
0038603	3 x 2 x 0.5	8.9	73.7	129
0038604	4 x 2 x 0.5	9.6	82	146
0038606	6 x 2 x 0.5	11.3	110	198
0038608	8 x 2 x 0.5	13.3	139	259
0038612	12 x 2 x 0.5	15.1	198.3	354
0038616	16 x 2 x 0.5	16.7	240	459
0038702	2 x 2 x 0.75	8.7	58	106
0038704	4 x 2 x 0.75	10.9	108	179
0038708	8 x 2 x 0.75	14.9	180	305
0038802	2 x 2 x 1.0	9.2	84	142
0038803	3 x 2 x 1.0	10.6	96	173
0038804	4 x 2 x 1.0	11.5	121	212

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16