

# UNITRONIC® ST

UL AWM 2092

UNITRONIC® ST: , , , EMC PVC ,



,

)

: IEC 60332-1-2

,가

(

UL AWM Style 2092 / 2093

7-가

: (PE)

가

PVC

,

:

/ 7001 RAL

.

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® ST

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	2 : , , 3 : , ,
:	C/C approx. 90 nF/km C/S approx. 160 nF/km
:	0.65 mH/km
:	: 10 x : 6 x
::	95 Ohm
:	: -5°C ~ +70°C : -40°C +80°C

가 가 ( . ) 가 .  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 : 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .



# UNITRONIC® ST

	AWG /	(mm <sup>2</sup> )			(mm)	(kg/km)
UNITRONIC® ST						
0033000	2 x AWG 20/7	0.52	PE	PVC	5.2	17.2
0033001	3 x AWG 20/7	0.52	PE	PVC	5.3	23

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16