



UNITRONIC® LiHCH

DIN 47100 , 가

UNITRONIC® LiHCH:

(0.34 mm²

Maxi TERMI-POINT®) DIN 47100,

가 가

CPR: www.lappkabel.com/cpr



: 가

가 가

: IEC 60332-1-2

(LSZH)

IEC 60754-1

, IEC 60754-2

가

/ ,

. EN 50305

가

IEC 61034-2

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® LIHCH

VDE 0812

/ 가 (0.34 mm²)

: (RAL 7032)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

DIN 47100 , T9

:

C/C approx. 80 nF/km
C/S approx. 120 nF/km

:

0.65 mH/km

:

0.34mm²: 7

:

: 10 x

: 6 x

:

1200 V

:

: -5°C ~ +70°C

: -30°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

TERMI-POINT® AMP

가 VAT 가 가 .

(24.04.2024)

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
UNITRONIC® LIHCH				
0037302	2 x 0.14	4.1	12	22
0037304	4 x 0.14	4.5	15.9	29
0037308	8 x 0.14	6	26	41
0037312	12 x 0.14	6.5	30.4	78
0037325	25 x 0.14	8.7	63	149
0037402	2 x 0.25	4.7	15	25
0037403	3 x 0.25	4.9	18	30
0037404	4 x 0.25	5.2	22	35
0037406	6 x 0.25	6.2	30	49
0037407	7 x 0.25	6.2	32	52
0037408	8 x 0.25	7.3	35	58
0037410	10 x 0.25	7.7	42	81
0037425	25 x 0.25	10.9	114	172
0037502	2 x 0.34	5.1	17	30
0037503	3 x 0.34	5.3	21	35
0037504	4 x 0.34	5.9	25	42
0037507	7 x 0.34	7	42	73
0037508	8 x 0.34	8	45	84
0037510	10 x 0.34	8.5	63	101
0037516	16 x 0.34	9.6	94	160
0037525	25 x 0.34	12.1	144	259
0037602	2 x 0.5	5.8	29	38
0037603	3 x 0.5	6.1	35	47
0037604	4 x 0.5	6.5	45	67
0037605	5 x 0.5	7.2	50	76
0037606	6 x 0.5	7.8	59	84
0037607	7 x 0.5	7.8	68	91
0037608	8 x 0.5	8.9	75	135
0037610	10 x 0.5	9.5	93	160
0037612	12 x 0.5	9.8	99	177
0037618	18 x 0.5	11.7	134	239
0037702	2 x 0.75	6.2	35	45
0037703	3 x 0.75	6.5	46	69

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



UNITRONIC® LIHCH

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
0037704	4 x 0.75	7.2	56	80
0037802	2 x 1.0	6.5	43	72
0037803	3 x 1.0	7	56	90
0037804	4 x 1.0	7.5	68	109
0037807	7 x 1.0	8.8	118	171
0037902	2 x 1.5	7.3	58	90
0037903	3 x 1.5	7.7	74	115

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16