

UNITRONIC® ROBUST C (TP)

DIN 47100

UNITRONIC® ROBUST C (TP):

/ / /

(Weather Resistance)

Good chemical resistance please see Appendix T1



가 , UV
가 ,

(24.04.2024)

UNITRONIC® ROBUST C (TP)

EN 50396 HD 605 S2 /UV / , IEC 60754-2 가 / , EN 50305 가
 IEC 60754-1 , IEC 60754-2 가 / , EN 50305 가
 IEC 61034-2

VDE 0812

/ 가 (0.34 mm²)

TP

TPE
 : (RAL 9005)

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	DIN 47100 , T9
:	C/C approx. 60 nF/km
:	C/S 100nF/km
:	> 20 GOhm x cm
:	0.65 mH/km
:	0.34mm ² : 7

WTG :	TW-0 & TW-2, T0
:	: 10 x
:	: 4 x
:	At 0.14 mm ² : 1200 V
:	: -40°C ~ +90°C
:	: -50°C +90°C

, 가 가 . (.) 가 .

(24.04.2024)



UNITRONIC® ROBUST C (TP)

www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

UNITRONIC® ROBUST C (TP)

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
UNITRONIC® ROBUST C (TP)				
1032100	2 x 2 x 0.14	5.3	16.1	31
1032101	3 x 2 x 0.14	5.8	19	38
1032102	4 x 2 x 0.14	6.2	23.1	46
1032103	5 x 2 x 0.14	6.4	27.2	54
1032104	6 x 2 x 0.14	7.1	31.3	63
1032105	8 x 2 x 0.14	8.2	43.4	90
1032106	10 x 2 x 0.14	8.7	50.9	93
1032107	12 x 2 x 0.14	8.9	56.6	102
1032108	2 x 2 x 0.25	6.3	22.7	43
1032109	3 x 2 x 0.25	7.1	28.9	56
1032110	4 x 2 x 0.25	7.6	38.3	72
1032111	5 x 2 x 0.25	7.9	45.1	85
1032112	6 x 2 x 0.25	8.5	48.7	96
1032113	8 x 2 x 0.25	10.3	64.3	135
1032114	2 x 2 x 0.34	7.1	27.6	56
1032115	3 x 2 x 0.34	7.8	38.8	74
1032116	4 x 2 x 0.34	8.4	47.5	90
1032117	5 x 2 x 0.34	8.8	58.2	110
1032118	1 x 2 x 0.5	5.6	20.1	37
1032119	2 x 2 x 0.5	7.9	40.3	72
1032120	3 x 2 x 0.5	8.7	51.7	91
1032121	4 x 2 x 0.5	9.4	64.1	112
1032122	5 x 2 x 0.5	10.3	76.6	141
1032123	6 x 2 x 0.5	11.1	91.7	170
1032124	8 x 2 x 0.5	13.1	123.2	238
1032125	10 x 2 x 0.5	14.5	146.4	247
1032126	2 x 2 x 0.75	8.5	48.4	84
1032127	3 x 2 x 0.75	9.4	68.9	114
1032128	4 x 2 x 0.75	10.7	86.2	149
1032129	6 x 2 x 0.75	12.1	131.9	225
1032130	8 x 2 x 0.75	14.7	168.2	315
1032131	2 x 2 x 1.0	9	64.1	98
1032132	3 x 2 x 1.0	10.4	83.5	135

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



UNITRONIC® ROBUST C (TP)

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1032133	4 x 2 x 1.0	11.3	105.7	168

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16