

JE-Y(ST)Y...BD

JE-Y (ST) Y ... VDE , VDE 0815, PVC, , , , / ,

DIN VDE 0815



. (. (IDC))
- (TP) (Crosstalk)

2 (2x2x0.8)
: IEC 60332-1-2
JE-Y (ST) Y ... BD EB:
IEC 60079-14: 2013/EN 60079-14: 2014/VDE 0165-1: 2014, 16.2.2 (i-) ,

DIN VDE 0815
JE-Y(ST)Y...BD

JE-Y(ST)Y...BD

PVC
2 가 , 4 (2 x 2 x 0.8)

Outer sheath made of PVC
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000829
	ETIM 5.0 : /
ETIM 6:	ETIM 6.0 Class-ID: EC000829
	ETIM 6.0 Class :
:	VDE 0815, T10
:	. 100 nF/km
:	200pF/100m
:	0.65 mH/km
:	- ()
	0.8 mm: 0.50 mm ²
:	: 6 x
:	Core/core: 500 V
	Core/screen: 2000 V
:	. 73.2 Ohm/km
:	Occasional flexing: -5°C ~ +50°C
	: -30°C +70°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



JE-Y(ST)Y...BD

	(mm) /	(mm)	(kg/km)	(kg/km)
JE-Y(ST)Y...BD				
0034190	2 x 2 x 0.8	6	25	60
0034191	4 x 2 x 0.8	8.5	45	96
0034192	8 x 2 x 0.8	11	85	158
0034193	12 x 2 x 0.8	13	126	225
0034194	16 x 2 x 0.8	14.5	166	290
0034195	20 x 2 x 0.8	16	206	350
0034197	40 x 2 x 0.8	22	407	660

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16