

UNITRONIC® LiHH

DIN 47100

가

UNITRONIC® LiHH:

LS0H/LSZH

0.34 mm²

Maxi TERMINAL®, DIN 47100,

가

가

CPR: www.lappkabel.com/cpr



:

가

가

가

: IEC 60332-1-2

(LSZH)

IEC 60754-1

, IEC 60754-2

가

/ ,

. EN 50305

가

IEC 61034-2

VDE 0812

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® LiHH

/ 가 (0.34 mm²)

: (RAL 7032)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

DIN 47100 , T9

:

80 nF/km

:

0.65 mH/km

:

0.34mm²: 7

:

: 10 x

: 6 x

:

1200 V

:

: -5°C ~ +70°C

: -30°C +80°C

가 가 (.) 가 .
: www.lappkabel.de/en/cable-standradlengths
30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

TERMI-POINT® AMP

가 VAT 가 가 .



UNITRONIC® LIHH

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
0037104	6 x 0.14	4.4	8.1	25
0037120	2 x 0.25	4	4.8	22
0037121	3 x 0.25	4.2	7.2	25
0037122	4 x 0.25	4.5	9.6	28
0037124	6 x 0.25	5.3	14.4	39
0037125	7 x 0.25	5.3	16.8	42
0037126	8 x 0.25	6.4	19.2	50
0037128	12 x 0.25	7.2	28.8	67
0037140	2 x 0.34	4.4	6.5	28
0037141	3 x 0.34	4.6	9.8	30
0037142	4 x 0.34	5	13.1	40
0037143	5 x 0.34	5.7	16.3	44
0037147	12 x 0.34	8	39.2	97
0037150	2 x 0.5	4.9	9.6	31
0037151	3 x 0.5	5.2	14.4	37
0037152	4 x 0.5	5.8	19.2	45
0037153	5 x 0.5	6.3	24	58
0037154	7 x 0.5	7.1	33.6	72
0037160	2 x 0.75	5.3	14.4	41
0037162	4 x 0.75	6.3	28.8	60
0037165	12 x 0.75	10.4	86.4	165
0037171	3 x 1.0	6.1	28.8	57
0037172	4 x 1.0	6.6	38.4	67

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16