




UNITRONIC® Li2YCY (TP) -

PE ,

UNITRONIC® Li2YCY (TP) fine-wire: LF, , PVC , DIN 47100, PE
RS422/RS485

RS485/RS422



- (TP) (Crosstalk)

10 가

RS422 RS485

가

UNITRONIC® Li2YCYv (TP) (Yv) 1.8 mm /

: IEC 60332-1-2

VDE 0812

:

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® Li2YCY (TP) -

: (PE)
TP

Outer sheath made of PVC
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	DIN 47100, T9
:	At 800 Hz: max. 60 nF/km
:	0.65 mH/km
:	, 가
:	: 15 x
:	: 6 x
- :	1 MHz 50 dB 10 MHz 40 dB
:	Core/core: 2000 V / : 1000 V
∴	100 ± 15 Ohm (> 1 MHz)
:	: -5°C ~ +70°C : -40°C +80°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: ≤ 30 kg or ≤ 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

UNITRONIC® Li2YCY (TP) -

	mm ² /	(mm)	(kg/km)	(kg/km)
UNITRONIC® Li2YCY (TP) -				
0031370	1 x 2 x 0.25	5.7	14	38
0031371	2 x 2 x 0.25	6.9	28	43
0031372	3 x 2 x 0.25	7.5	39.6	64
0031373	5 x 2 x 0.25	8.3	50	93