

UNITRONIC® Li2YCY (TP)

PE , 7-가

UNITRONIC® Li2YCY (TP): DIN 47100 PE , RS422/RS485
PVC

RS485/RS422



- (TP) (Crosstalk)

10 가

RS422 RS485

가

UNITRONIC® Li2YCYv (TP) (Yv) 1.8 mm /

: IEC 60332-1-2

VDE 0812

7-가

(24.04.2024)

UNITRONIC® Li2YCY (TP)

TP : (PE)

Outer sheath made of PVC
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	DIN 47100, T9
:	At 800 Hz: max. 60 nF/km
:	0.65 mH/km
:	, VDE 0881 , 7
:	: 15 x
:	: 6 x
- :	1 MHz 50 dB 10 MHz 40 dB
:	Core/core: 2000 V / : 1000 V
∴	100 ± 15 Ohm (> 1 MHz)
:	: -5°C ~ +70°C : -40°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).
TERMI-POINT® AMP

가 VAT 가 가



UNITRONIC® Li2YCY (TP)

	mm ² /	(mm)	(kg/km)	(kg/km)
UNITRONIC® Li2YCY (TP)				
0031320	2 x 2 x 0.22	6.5	24.2	59
0031321	3 x 2 x 0.22	7.1	28.6	66
0031322	4 x 2 x 0.22	7.3	34.2	78
0031323	8 x 2 x 0.22	9.1	70	125
0031324	10 x 2 x 0.22	10.4	76	143
0031335	1 x 2 x 0.34	5.8	20	44
0031325	2 x 2 x 0.34	7.7	34.1	79
0031326	3 x 2 x 0.34	8.4	43	89
0031327	4 x 2 x 0.34	8.7	47	101
0031328	8 x 2 x 0.34	11	85.8	176
0031336	1 x 2 x 0.5	6.3	29	53
0031330	2 x 2 x 0.5	8.5	37	85
0031331	3 x 2 x 0.5	9.3	55	105
0031332	4 x 2 x 0.5	9.6	60	122
0031333	8 x 2 x 0.5	12.7	113.3	213
0031334	10 x 2 x 0.5	14.8	154	261

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16