

# UNITRONIC® ROBUST C

DIN 47100

UNITRONIC® ROBUST C:

/ / /

, -40 ~ +90°C

(Weather Resistance)

Good chemical resistance please see Appendix T1



가 , UV  
가 ,

(24.04.2024)

# UNITRONIC® ROBUST C

EN 50396 HD 605 S2 /UV / , IEC 60754-2 가 / , . EN 50305 가  
 IEC 60754-1 , IEC 60754-2 가 / ,  
 IEC 61034-2

VDE 0812

/ 가 (0.34 mm<sup>2</sup>)

TPE

:

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

:

DIN 47100 , T9

:

C/C approx. 60 nF/km

C/S : 100nF/km

:

> 20 GOhm x cm

:

0.65 mH/km

:

0.34mm<sup>2</sup>: 7

WTG

:

TW-0 & TW-2, T0

:

: 10 x

: 4 x

:

At 0.14 mm<sup>2</sup>: 1200 V

:

: -40°C ~ +90°C

: -50°C +90°C

www.lappkabel.de/en/cable-standradlengths 가 가 ( . ) 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# UNITRONIC® ROBUST C

: 30 kg or 250 m, (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)

UNITRONIC® ROBUST C

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
UNITRONIC® ROBUST C				
1032050	2 x 0.14	3.9	9.3	25
1032051	3 x 0.14	4.1	10.8	28
1032052	4 x 0.14	4.3	13.5	34
1032053	5 x 0.14	4.6	15	38
1032055	7 x 0.14	4.9	19	46
1032056	8 x 0.14	5.8	22	60
1032057	10 x 0.14	6.1	25.8	63
1032058	12 x 0.14	6.3	28.9	70
1032061	25 x 0.14	8.4	56.1	128
1032062	2 x 0.25	4.5	12.7	33
1032063	3 x 0.25	4.7	16.3	40
1032064	4 x 0.25	5	18.8	46
1032065	5 x 0.25	5.6	22.5	57
1032067	7 x 0.25	6	28.6	69
1032068	8 x 0.25	7.1	33.6	92
1032069	10 x 0.25	7.5	42.8	101
1032070	12 x 0.25	7.7	47.7	111
1032073	25 x 0.25	10.6	86.5	202
1032074	2 x 0.34	4.9	15.7	44
1032075	3 x 0.34	5.1	20.4	54
1032076	4 x 0.34	5.7	23.6	66
1032077	5 x 0.34	6.2	28.2	78
1032079	7 x 0.34	6.8	36	95
1032080	8 x 0.34	7.8	45.3	127
1032081	10 x 0.34	8.3	53.9	137
1032082	12 x 0.34	8.5	60.7	152
1032084	16 x 0.34	9.4	77.9	191
1032086	25 x 0.34	11.9	115.7	288

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16