

UNITRONIC® 300 STP

- UL/CSA

UNITRONIC® 300 STP: PVC , UL/CSA AWM, CMG, , -25°C ~ 105°C
Further Tray

가
20AWG 18AWG: 37 가 / (: - , 50)



- (TP) (Crosstalk)

(30.04.2024)

UNITRONIC® 300 STP

CMG, PLTC ITC 가 6 -ER
 (Exposed Run)
 DIRECT BURIAL 18 AWG
 ± 150°/ m

UL OIL RES I

USA: (UL) CMG [E130334], (UL) PLTC-ER (18 AWG) [E216027], (UL) PLTC (>24 AWG) [E216027], (UL) ITC-ER (18 AWG) [E196134], UL AWM Style 2464 [E100338], DIR BUR (18 AWG)
 CAN: c(UL) CMG FT4 [E130334], CSA AWM I/II A/B FT1

PVC
 TP

: PVC, (RAL 7005) (75%)

ETIM 5: ETIM 5.0 Class-ID: EC000830
 ETIM 5.0 Class- :

ETIM 6: ETIM 6.0 Class-ID: EC000830
 ETIM 6.0 Class :

:
 Pair 1: ,
 Pair 2: ,
 Pair 3: ,
 Pair 4: ,
 Pair 5: ,
 Pair 6: ,
 , 24-22 AWG: ,

WTG : TW-0 & TW-2, T0
 : 15 x
 : 6 x

: UL: 300 V
 IEC:
 : 1500 V

: -25°C~+105°C
 Fixed installation/ North America: -40°C to +105°C (AWM for USA: +80°C)

가 가 () 가
 www.lappkabel.de/en/cable-standradlengths
 : 152 m; 305 m

(30.04.2024)



UNITRONIC® 300 STP

가 VAT 가 가 .

(30.04.2024)



UNITRONIC® 300 STP

	() x AWG	(mm)	[kg/km]	[kg/km]
UNITRONIC® 300 STP				
302402STP	2 x 2 x 24 AWG	6.5	25.5	59
302403STP	3 x 2 x 24 AWG	6.8	31.1	65
302406STP	6 x 2 x 24 AWG	8.7	49.7	106
302201STP	1 x 2 x 22 AWG	5.1	19.1	39
302203STP	3 x 2 x 22 AWG	7.7	38.2	71
302206STP	6 x 2 x 22 AWG	9.6	70	125
302002STP	2 x 2 x 20 AWG	9.4	47.7	128
302003STP	3 x 2 x 20 AWG	10.5	68.2	161
302006STP	6 x 2 x 20 AWG	13.3	106.5	321
301801STP	1 x 2 x 18 AWG	6.8	37.8	106
301802STP	2 x 2 x 18 AWG	10.7	66.2	122
301806STP	6 x 2 x 18 AWG	14.6	153.1	324

(30.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16