

UNITRONIC® ROBUST

DIN 47100

UNITRONIC® ROBUST:

, -40°C ~ +90°C,

(Weather Resistance)

Good chemical resistance please see Appendix T1



CE UK CA ROSLAN



가 , , UV
가 , ,

(24.04.2024)

UNITRONIC® ROBUST

EN 50396 HD 605 S2 /UV / , IEC 60754-2 가 / , . EN 50305 가
 IEC 60754-1 , IEC 60754-2 가 / ,
 IEC 61034-2

VDE 0812

/ 가 (0.34 mm²)

TPE
:

ETIM 5: ETIM 5.0 Class-ID: EC000830
 ETIM 5.0 Class- :
 ETIM 6: ETIM 6.0 Class-ID: EC000830
 ETIM 6.0 Class :
 : DIN 47100 , T9
 : C/C approx. 60 nF/km
 : > 20 GOhm x cm
 : 0.65 mH/km
 :
 : 0.34mm²: 7

WTG : TW-0 & TW-2, T0
 : : 10 x
 : 4 x
 : At 0.14 mm²: 1200 V
 : : -40°C ~ +90°C
 : -50°C +90°C

가 가 (.) 가 .
 : www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m, (e.g. 1 x 500 m or 5 x 100 m).

(24.04.2024)



UNITRONIC® ROBUST

가 VAT 가 가 .

(24.04.2024)



UNITRONIC® ROBUST

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
UNITRONIC® ROBUST				
1032000	2 x 0.14	3.2	2.8	15
1032001	3 x 0.14	3.4	4.2	17
1032002	4 x 0.14	3.6	5.6	21
1032003	5 x 0.14	3.9	7	25
1032004	7 x 0.14	4.2	9.8	30
1032005	8 x 0.14	4.9	11.2	40
1032006	10 x 0.14	5.2	14	41
1032007	12 x 0.14	5.6	16.8	50
1032009	16 x 0.14	6.1	22.4	63
1032011	25 x 0.14	7.7	35	95
1032012	2 x 0.25	3.8	4.8	21
1032013	3 x 0.25	4	7.2	25
1032014	4 x 0.25	4.3	9.6	31
1032015	5 x 0.25	4.7	12	38
1032016	7 x 0.25	5.1	16.8	47
1032017	8 x 0.25	6.2	19.2	66
1032018	10 x 0.25	6.8	24	71
1032019	12 x 0.25	7	28.8	81
1032021	16 x 0.25	7.7	38.4	104
1032024	25 x 0.25	9.5	60	151
1032025	2 x 0.34	4.2	6.5	29
1032026	3 x 0.34	4.4	9.8	32
1032027	4 x 0.34	4.8	13.1	41
1032028	5 x 0.34	5.5	16.3	52
1032030	7 x 0.34	5.9	22.9	65
1032031	8 x 0.34	7.1	26.1	90
1032032	10 x 0.34	7.6	32.6	93
1032033	12 x 0.34	7.8	39.2	107
1032035	16 x 0.34	8.7	52.2	138
1032038	25 x 0.34	11.2	81.6	213

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16