



UNITRONIC® LiYCY (TP) A

UL/CSA- DIN 47100 , 가
UNITRONIC® LiYCY (TP) A: PVC DIN 47100, UL CSA AWM, , 0.34² Maxi TERMI-POINT®,

: UL CSA
가 가



- (TP) (Crosstalk)

UL-/CSA 가 ,

IEC 60332-1-2, UL VW-1 CSA FT 1

UL AWM Style 2464
CSA AWM I/II A
UL File No. E63634

PVC

(23.04.2024)

UNITRONIC® LiYCY (TP) A

TP

PVC : (RAL 7005)

ETIM 5: ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

: DIN 47100 , T9

: : 15 x

: 6 x

: UL/CSA: 300 V

: 1500 V

: Occasional flexing: -5°C up to +70°C (UL: +80 °C)

Fixed installation (IEC): -40°C bis +80°C

UL: max. +80°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths

: 152 m; 305 m

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® LIYCY (TP) A

	AWG /	(mm)	[kg/km]	[kg/km]
UNITRONIC® LIYCY (TP) A				
0066202	2 x 2 x AWG26/7	5.5	18	38
0066204	4 x 2 x AWG26/7	6.4	24	58
0066205	5 x 2 x AWG26/7	6.6	30	58
0066208	8 x 2 x AWG26/7	7.9	53	85
0066210	10 x 2 x AWG26/7	8.7	55	106
0066212	12 x 2 x AWG26/7	8.9	64	113
0066216	16 x 2 x AWG26/7	10.2	87	149
0066232	2 x 2 x AWG24/7	6.1	24.5	50
0066233	3 x 2 x AWG24/7	6.7	28.9	62
0066234	4 x 2 x AWG24/7	7.2	33.5	70
0066235	5 x 2 x AWG24/7	7.5	46.3	91
0066238	2 x 2 x AWG22/7	7.4	38	71
0066239	3 x 2 x AWG22/7	8.1	45.1	95
0066240	4 x 2 x AWG22/7	8.8	54.6	102
0066242	2 x 2 x AWG20/7	8.2	49.7	93
0066243	3 x 2 x AWG20/7	9.1	60.1	102
0066244	4 x 2 x AWG20/7	10.2	78.7	120
0066219	5 x 2 x AWG20/7	10.7	88.9	156
0066220	6 x 2 x AWG20/7	11.6	100.6	184
0066262	2 x 2 x AWG19/19	8.7	65.2	140
0066221	3 x 2 x AWG19/19	10	69.2	145

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16