

UNITRONIC® Li2YCY PiMF

PE

가

UNITRONIC® Li2YCY PiMF:
PVC

, RS422/RS485

DIN 47100

PE



- (TP) (Crosstalk)

()
27+

: IEC 60332-1-2

7-wire fine-wire (1 mm²)

: (PE)

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® Li2YCY PiMF

Outer sheath made of PVC

Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	0.22mm ² ~0.5mm ² :
:	DIN 47100 , T9 1.0 mm? a- : , b- :
:	800Hz: 0.22mm ² : 70nF/km 0.34mm ² : 70nF/km 0.5mm ² : 75nF/km 1.0mm ² : 85nF/km
:	0.4 mH/km
:	, VDE 0881 , 7
:	: 20 x : 10 x
:	Core/core: 2000 V / : 1000 V
∴	85 (> 1MHz)
:	: -5°C ~ +70°C : -40°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

TERMI-POINT® AMP

가 VAT 가 가

(25.04.2024)



UNITRONIC® Li2YCY PiMF

	mm ² /	(mm)	(kg/km)	(kg/km)
UNITRONIC® Li2YCY PiMF				
7-가				
0034040	2 x 2 x 0.22	7.7	33	75.4
0034041	3 x 2 x 0.22	8.1	42	86
0034042	4 x 2 x 0.22	8.7	50	99
0034043	8 x 2 x 0.22	10.9	85	161.4
0034044	10 x 2 x 0.22	12	100	186.4
0034045	2 x 2 x 0.34	9	43	70
0034046	3 x 2 x 0.34	9.4	55	85
0034047	4 x 2 x 0.34	9.8	64	103
0034048	8 x 2 x 0.34	12.9	127	191
0034060	2 x 2 x 0.5	9.9	51	96
0034061	3 x 2 x 0.5	10.4	66	116
0034062	4 x 2 x 0.5	11.3	71	141
0034063	5 x 2 x 0.5	11.8	92	180
0034064	8 x 2 x 0.5	14.5	153	271
0034065	10 x 2 x 0.5	16.6	182	327
0034070	2 x 2 x 1	11.7	82	126
0034071	3 x 2 x 1	11.8	109	196
0034072	4 x 2 x 1	12.7	133	220
0034073	10 x 2 x 1	19.7	326	492

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16