

UNITRONIC® Li2YCYv (TP)

PE ,

UNITRONIC® Li2YCYv (TP): PVC , DIN 47100 PE ,
/ , RS422/RS485

RS485/RS422



- (TP) (Crosstalk)

10 가

RS422 RS485

가

UNITRONIC® Li2YCYv (TP) (Yv) 1.8 mm /

: IEC 60332-1-2

VDE 0812

7-가

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® Li2YCYv (TP)

TP : (PE)

가 가 ("Yv")
: (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

DIN 47100, T9

:

At 800 Hz: max. 60 nF/km

:

0.65 mH/km

:

, VDE 0881 , 7

:

: 15 x

: 6 x

- :

1 MHz 50 dB

10 MHz 40 dB

:

Core/core: 2000 V

/ : 1000 V

∴

100 ± 15 Ohm (> 1 MHz)

:

: -5°C ~ +70°C

: -40°C +80°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: ≤ 30 kg or ≤ 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

UNITRONIC® LI2YCYV (TP)

	mm ² /	(mm)	(kg/km)	(kg/km)
UNITRONIC® Li2YCYV (TP), strengthened outer sheath "Yv", and black for outdoor installation/ technical UV resistance, 7-wire				
0031350	2 x 2 x 0.22	8.1	24.2	79
0031351	3 x 2 x 0.22	8.4	28.6	93
0031352	4 x 2 x 0.22	8.9	34.2	100
0031353	8 x 2 x 0.22	10.7	70	156
0031354	10 x 2 x 0.22	12	76	185
0031365	1 x 2 x 0.34	7.4	20	69
0031355	2 x 2 x 0.34	9.3	34.1	102
0031356	3 x 2 x 0.34	10	43	117
0031357	4 x 2 x 0.34	10.3	52.8	130
0031358	8 x 2 x 0.34	12.6	85.8	206
0031366	1 x 2 x 0.5	7.9	29	79
0031360	2 x 2 x 0.5	10.1	37	120
0031361	3 x 2 x 0.5	10.9	55	142
0031362	4 x 2 x 0.5	11.2	60	160
0031363	8 x 2 x 0.5	13.9	113.3	251
0031364	10 x 2 x 0.5	16	148	303