

# J-H(ST)H...BD

DIN VDE 0815

J-H(ST)H...BD - VDE 0815

DIN VDE 0815



J-H(ST)H...BD 가 ( )  
- (TP) (Crosstalk ) ( ) " "

가 가 , ,

Flame retardant acc. to DIN VDE 0472-804/08.83, Test method C  
EN 50267-2-1/-2

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# J-H(ST)H...BD

DIN VDE 0815  
e J-H(ST)H...BD

,5 가 ,  
( ), : (RAL 7001)

ETIM 5:	ETIM 5.0 Class-ID: EC000829 ETIM 5.0 : /
ETIM 6:	ETIM 6.0 Class-ID: EC000829 ETIM 6.0 Class :
:	VDE 0815, T10
:	. 120 nF/km
:	K1: 300 pF/100 m K9-12: 100 pF/100 m
:	: 8 x
:	Core/core: 800 V Core/screen: 800 V
:	0.6 mm: . 130 ohm/km 0.8 mm: . 73.2 ohm/km
:	0.6 mm: 0.28 mm <sup>2</sup> 0.8 mm: 0.50 mm <sup>2</sup>
:	Occasional flexing: -5°C ~ +50°C : -30°C +70°C

, 가 가 . ( . ) 가 .  
: [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
30 kg or 250 m,

가 VAT 가 가 .

(01.05.2024)



J-H(ST)H...BD

	( ) x ( ) x (mm)	(mm)	(kg/km)	(kg/km)
30017787	2 x 2 x 0.8	7	25	77
30017788	4 x 2 x 0.8	9.2	45	135

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16