

# UNITRONIC® 100 CY

가

UNITRONIC® 100 CY: PVC , LAPP UNITRONIC® , , , ,



가

UNITRONIC® 100 가

: IEC 60332-1-2

3 ( - )  
2 ( / )

: VDE 0814 VDE 0812

/ 가 (0.34 mm<sup>2</sup>)

PVC

PVC

0.14 mm<sup>2</sup> , 가

PVC

: (RAL 7001)

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® 100 CY

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	UNITRONIC® T17
:	120 nF/km
:	0.7 mH/km
:	0.34mm <sup>2</sup> : 7
:	: 20 x
:	: 6 x
:	-
:	: -5°C ~ +70°C
:	: -40°C +80°C

가 가 ( ) 가  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 : 30 kg or 250 m, (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(23.04.2024)



UNITRONIC® 100 CY

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
UNITRONIC® 100 CY				
0034006	2 x 0.14	3.7	12	20
0034007	3 x 0.14	3.9	13	28
0034008	4 x 0.14	4.1	14.3	33
0034009	5 x 0.14	4.4	15.5	38
0034010	7 x 0.14	4.7	20.3	49
0034011	10 x 0.14	5.7	34.3	66
0034012	14 x 0.14	6.3	32	80
0034013	16 x 0.14	6.6	40.9	90
0034016	27 x 0.14	8.1	70.6	148
0031031	3 x 0.25	5.4	20.2	48
0031066	4 x 0.25	5.7	24	61
0031067	5 x 0.25	6.3	29	72
0031032	7 x 0.25	6.7	37.6	82
0031033	10 x 0.25	8.2	48.8	129
0031034	14 x 0.25	8.7	64.6	147
0031068	2 x 0.34	5.6	20	45
0031048	3 x 0.34	5.8	24.1	62
0031069	4 x 0.34	6.4	29	65
0031070	5 x 0.34	6.9	42	95
0031049	7 x 0.34	7.3	50	106
0031050	10 x 0.34	9	67.7	167
0031052	16 x 0.34	10.5	95	219
0031060	52 x 0.34	17.6	336	629

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16