

A-2YF(L)2Y...ST III BD

A-2YF (L) 2Y ... ST III BD - , VDE 0816 , / /



UV : (RAL 9005)

A-2YF(L)2Y...ST III BD 가 가

DIN VDE 0816

A-2Y(L)2Y , - , PE

ETIM 5: ETIM 5.0 Class-ID: EC000829
ETIM 5.0 : /

ETIM 6: ETIM 6.0 Class-ID: EC000829
ETIM 6.0 Class :

: VDE 0816 ,

(24.04.2024)

A-2YF(L)2Y...ST III BD

T10

:	At 800 Hz: max. 52 nF/km
:	K1: 98 % <400 pF/300 m
:	K9-12: 98 % < 100 pF/300 m
in:	0.6 mm: 0.28 mm ²
	0.8 mm: 0.50 mm ²
/ :	At 800 Hz 0.6 mm: approx. 1.0 dB/km
	At 800 Hz 0.8 mm: approx. 0.8 dB/km
:	10 x
:	Core/core: 500 V
:	Core/screen: 2000 V
:	0.6 mm: 130 ohm/km
:	0.8 mm: 73.2 ohm/km
:	: -20 °C to +50 °C
	: +70 °C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,

가 VAT 가 가 .

(24.04.2024)



A-2YF(L)2Y...ST III BD

	()	(mm)	[kg/km]	[kg/km]
A-2YF(L)2Y...ST III BD 0.6 mm				
1591028	2	8.3	11	67
1591029	4	10.4	23	104
1591030	6	11	34	130
1591031	10	12.5	57	180
1591032	20	16	113	300
1591033	30	19	170	420
1591035	50	22.3	283	620
1591037	100	30.5	565	1225
A-2YF(L)2Y...ST III BD 0.8 mm				
1591217	2	8.8	20	83
1591218	4	11.2	40	134
1591221	6	12	60	180
1591222	10	14	101	250
1591223	20	19.1	201	460
1591224	30	22	302	630
1591225	40	24	402	800
1591226	50	26	503	975
1591228	100	36	1005	1900

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16