

EPIC® SIGNAL M23 D6

Servo

EPIC® M23

EMC 가
Made in Germany



SKINTOP®

- , EMC

(23.04.2024)

EPIC® SIGNAL M23 D6

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

:

: - -

: FPM

가:

IP68 (10h/1m)

VDE- :

: VDE-REG. C24(EN 61984 , DIN

VDE 0100-410 SELV가)

UL : E249137

:

-25°C ~+125°C

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® SIGNAL M23 D6

	Article			/ PU
M23 D6				
44420037	M23 D6	(N)	7 - 13.5	5
75018413	M23 D6	(N)	5.0 - 7.3	5
72044030	M23 D6	(N)	7 - 10	5
72044020	M23 D6	(N)	7 - 10	20
72044000	M23 D6	(N)	9.5 - 13.5	5
72044010	M23 D6	(N)	9.5 - 13.5	20
44420038	M23 D6	(+20°)	7 - 13.5	5
72044230	M23 D6	(+20°)	7 - 10	5
72044220	M23 D6	(+20°)	7 - 10	20
72044200	M23 D6	(+20°)	9.5 - 13.5	5
72044210	M23 D6	(+20°)	9.5 - 13.5	20
44420036	M23 D6	(-20°)	7 - 13.5	5
72044130	M23 D6	(-20°)	7 - 10	5
72044120	M23 D6	(-20°)	7 - 10	20
72044100	M23 D6	(-20°)	9.5 - 13.5	5
72044110	M23 D6	(-20°)	9.5 - 13.5	20

(23.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® SIGNAL M23 D6



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16