


UNITRONIC® SENSOR master cable

가 S/A

가



Lapp



S/A 가 가 S/A

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR master cable

3 x 0.75 mm² and 3 x 1.0 mm²

4 x 0.34 mm², 8 x 0.5 mm², 16 x 0.5 mm²

VDE 0472-815
: UL 1581 FT-2

UL-AWM-Style 21198 (80 °C / 300 V)

0.15 mm) : 0.34 mm² = (43 x 0.10 mm), 0.5mm² = (19 x 0.18 mm), 0.75 mm² = (21 x 0.205 mm), 1.0 mm² = (55 x 0.15 mm)
: PP
: PUR,

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	, 가
:	: 10 x
:	: -40°C +80°C
	: -5°C +80°C

: 100m , 가 가 . (.) 가 .
가 VAT 가 가 .



UNITRONIC® SENSOR master cable

		Dimensions (mm ²)	(mm)	/	[kg/km]
UNITRONIC® SENSOR COMBI					
7038880	Li9Y11Y	3 x 0.75 + 4 x 0.34	6.6	PP/PUR	34.5
7038881	Li9Y11Y	3 x 1.0 + 8 x 0.5	8.4	PP/PUR	67.2
7038882	Li9Y11Y	3 x 1.0 + 16 x 0.5	9.8	PP/PUR	105.6

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR master cable



(24.04.2024)