

EPIC® H-A 3 MTGVB

가

UL50E



The EPIC® H-A 3 series comprises the smallest housings in the heavy-duty industrial connector range and ensures secure connections in the smallest of spaces.

The coupling housing is mateable with many commercially available hood housings.

The integrated SKINTOP® cable gland made of brass is used for sealing and strain-relieving cable entry. Compared to enclosures where the cable gland is added separately, the overall size of the enclosure is more space-saving.

The locking is done single lever.

The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.

To protect the connector insert from environmental influences.

For use with many EPIC® rectangular connector inserts.

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-A 3 MTGVB

For power supply connection of devices and machines in various applications.
Withstands high environmental and mechanical stresses.

1

가 /

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

:

: - - ,

:

가:

IP 65 (latched)

NEMA 250, UL50E: 12, 4 (latched)

VDE- :

: VDE-REG. : B437

UL- :

UL : E75770

:

-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-A 3 MTGVB

	Article description	M	PG					/ PU
H-A : ()								
10512900	H-A 3 MTgvb	-	11	-	-	-	-	10
10429500	H-A 3 MTgvb	-	11	-	yes	-	6.5 - 12	10
19512900	EPIC® H-A 3 MTgvb M20	20	-	-	-	-	-	10
19429500	EPIC® H-A 3 MTgvb M20	20	-	-	yes	-	3.0 - 13.5	10

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-A 3 MTGVB



(23.04.2024)