

EPIC® POWER M12L G4

Virtually conceived and now in real life: The M12 power connector with L-coding meets all market requirements. It is very small yet powerful, prevents mismatching, is PROFINET-compliant. With M12L, sensor/actuator cabling as well as the power supply of smaller DC motors, e.g. in driverless transport systems, is successful.



Lapp



Attachment housing G4 in combination with coupling plug F6.
Powerful up to 16 A despite extremely space-saving size for very small devices.
Mechanical L-coding of the mating face prevents mismatching with mating connector.
Suitable for conductor cross-sections from 0.75 - 2.50 mm².

Available as 4-pole variant with black insulating body and as 4+FE variant with grey insulating body and functional earth contact (FE).

For DC applications in the low-voltage range.
For power supply of smaller devices (e.g. decentralised I/O modules, smaller motors).
Also suitable for power supply in the PROFINET network (M12L is considered the standardised power interface there).

(20.07.2024)

EPIC® POWER M12L G4

ETIM 5:	ETIM 5.0 Class-ID: EC002635
ETIM 6:	ETIM 6.0 Class-ID: EC002635
(V):	63 V
:	1.5 kV
(A):	16 A
:	3
/ :	4, 4+PE
:	0.75mm ² - 2.5mm ²
:	:
:	: PA,
:	: FPM
가:	IP65/IP67/IP69
:	100
:	-25°C ~+125°C

가 VAT 가 가 .

(20.07.2024)



EPIC® POWER M12L G4

				Packaging unit
44423156	5	M12	4+PE	1
44423420	-	M12	4+PE	20
44423150	4	M12	4	1
44423416	-	M12	4	20

(20.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16