

EPIC® POWER M17 D6

EPIC® M17 POWER

Made in Germany



/ ac

EMC

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® POWER M17 D6

ETIM 5:	ETIM 5.0 Class-ID: EC002635
	ETIM 5.0 class : ()
ETIM 6:	ETIM 6.0 Class-ID: EC002635
	ETIM 6.0 Class : ()
(V):	630V: 2mm 1mm
	60V: 0.6mm
:	6KV: 2mm 1mm
	1.5KV: 0.6mm
(A):	3+PE: 20A, 5+PE/6+PE/7+PE:14A, 3+PE+5:14A/3,6A
:	3
:	
/ :	3+PE, 5+PE, 6+PE, 7+PE, 3+PE+5
	:3+PE(2mm), 5+PE(1mm), 6+PE(1mm), 7+PE(1mm),
	3+PE+5(1mm/0.6mm)
:	: 3+PE: 0.5-2.5mm ² , 5+PE/6+PE/7+PE: 0.06-1mm ² ,
	3+P+5: 0.06-1/0.06-0.5mm ²
:	:
	: PA,
	: FPM
가:	IP 67
:	100
:	-40°C +125°C

가 VAT 가 가 .

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® POWER M17 D6

	Article description	Clamping range min	Clamping range max		/ PU
M17 D6,					
44423050	EPIC® M17	3.5	11	3+PE (2mm)	5
44423055	EPIC® M17	3.5	11	3+PE (2mm)	5
44423051	EPIC® M17	3.5	11	5+PE (1mm)	5
44423056	EPIC® M17	3.5	11	5+PE (1mm)	5
44423052	EPIC® M17	3.5	11	6+PE (1mm)	5
44423057	EPIC® M17	3.5	11	6+PE (1mm)	5
44423053	EPIC® M17	3.5	11	7+PE (1mm)	5
44423058	EPIC® M17	3.5	11	7+PE (1mm)	5
44423059	EPIC® M17	3.5	11	3+PE+5 (1mm/0.6mm)	5

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® POWER M17 D6



(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16