

EPIC® SIGNAL R 3.0 D PG16

, 21- , 26- 가

EPIC® R3.0 26

Made in Germany



ETIM 5:

ETIM 5.0 Class-ID: EC002635

ETIM 5.0 class : ()

ETIM 6:

ETIM 6.0 Class-ID: EC002635

ETIM 6.0 Class : ()

(V):

24V AC / 60VDC

:

1.5 kV

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® SIGNAL R 3.0 D PG16

| | |
|------|--|
| (A): | 7.5 A |
| : | < 3 mOhm |
| : | , |
| / : | 21- / 26- |
| : | : 1.0 mm ² |
| : | : - |
| : | : 가 |
| : | : |
| 가: | IP 67 (,) |
| : | 500 |
| : | -40°C to +100°C, short-term up to +125°C |

가

가 VAT 가 가 .

(23.04.2024)



EPIC® SIGNAL R 3.0 D PG16

| | Article | Version | | | | | / PU |
|--------------|----------------|---------|--------|--------|---|----------|------|
| R 3.0 D PG16 | | | | | | | |
| 00009045 | SIGNAL R 3.0 D | | 1 - 21 | E-Part | N | 6.5 - 16 | 5 |
| 00008899 | SIGNAL R 3.0 D | | 1 - 26 | E-Part | N | 6.5 - 16 | 5 |
| 00008749 | SIGNAL R 3.0 D | | 1 - 21 | P-Part | N | 6.5 - 16 | 5 |
| 00008829 | SIGNAL R 3.0 D | | 1 - 26 | P-Part | N | 6.5 - 16 | 5 |

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16