

EPIC® ASC axial screw contact

EPIC®

Axial screw contact for high current module modul EPIC® MH 1 250A, suitable for cross section from 35mm² up to 70mm², service-friendly connection without any special tool.

EPIC® ASC contact as an alternative to the crimping contact.

Axial screw contact for assembly with low-cost tools.



Lapp



Axial screw contact that can be freely rotated in the high-current module simplifies assembly, prevents torsional stress and thus ensures contact reliability between contact and wire.

Assembly of the contact outside the module enables visual inspection of the connection and thus eliminates the failure potential of insufficient overlapping between contact and wire.

Silver-plated contact surface for low contact resistance and minimal heat generation at the contact.

Axial screw clamp technology allows service-friendly connection without special crimping tool, saves costs and is suitable for removable connections.

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® ASC axial screw contact

Simple conductor connection by means of hexagon socket and open-end wrench.
Only one axial screw contact required for conductor cross-sections from 35 to 70 mm².

Axial screw contact can be used in existing high-current module as an alternative to crimp contact.
Connection of the high-current module with axial screw contact ensures maximum safety for the user due to contact protection.

：	< 0.3 mOhm
：	Crimp termination: 35 mm ² ... 70 mm ²
：	brass silver plated CuZn / Ag
：	500
：	-40°C ~ +120°C

가 VAT 가 가 .

(24.04.2024)



EPIC® ASC axial screw contact

	Article description	Version	/ PU
44423397	EPIC® ASC SSEM AG 35-70mm ² D=10.0mm		10
44423396	EPIC® ASC BSEM AG 35-70mm ² D=10.0mm		10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16