

EPIC® H-Q TG

There are many different uses for this sturdy rectangular connector hood made of plastic. The M25 female thread is suitable for connecting a separate cable or conduit gland. This results in an optimised design with regard to weight and installation space.



The hood housing is mateable with many commercially available housings (panel-mount base, surface-mount base or coupler hood housings).

Space and weight-saving due to the small size.

With space-saving female thread for use with metric cables or conduit glands.

Locking takes place using a central lever on the counter-housing.

Corresponds to protection class IP 65 when locked.

To protect the connector insert from environmental influences.

For use with rectangular connector inserts in the EPIC®H-Q series.

For power supply connection of devices and machines in various applications.

Withstands high environmental and mechanical stresses.

Typical areas of application are electric motors and servo drives.

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

:

: 가 ,

:

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-Q TG

가: IP 65
: -40°C +125°C

가 VAT 가 가 .

(22.07.2024)



EPIC® H-Q TG

	M	Packaging unit
381166440	25	10

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16