

EPIC® H-A 3 TG

Locks reliably, does not burn, and protects the internal insert from dust and moisture: these are just three of the essential features of our newly revamped rectangular connector housing. The lightweight polyamide hood is also halogen-free, UV-resistant and has an M20 thread for connecting a cable or conduit gland.

The hood of the EPIC® H-A 3 series is now available with a new design, including a marking arrow and an M20 thread.



The EPIC® H-A 3 series comprises the smallest housings in the heavy-duty industrial connector range and ensures secure connections in the smallest of spaces.

The hood housing is mateable with many commercially available housings (panel-mount base, surface-mount base or coupler hood housings).

With threaded hole for use with a corresponding cable gland.

Articles with a "V" in the article name already contain a SKINTOP® plastic cable gland for sealing and strain-relieving cable entry. In comparison to housings where the cable gland is added separately, the overall size of this housing is more space-saving.

The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.

(24.04.2024)

EPIC® H-A 3 TG

To protect the connector insert from environmental influences.
For use with many EPIC® rectangular connector inserts.

For connecting devices and machines to the power supply.
Suitable for outdoor use.

가 /

ETIM 5:

ETIM 5.0 Class-ID: EC000437
ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437
ETIM 6.0 Class-Description: Housing for industrial connectors

:

: ,
: -

가:

IP 65 (latched)
NEMA 250, UL50E: 12, 4 (latched)

VDE- :

: VDE-REG. : B437

UL- :

UL : E75770

:

-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .

(24.04.2024)



EPIC® H-A 3 TG

	Article description	M	PG					/ PU
10426000	H-A 3 TG PG11 gr	-	11			-	-	10
10425500	H-A 3 TG PG11 bk	-	11			-	-	10
10426400	H-A 3 TGV PG11 gr	-	11			yes	6.5 - 12	10
10426700	H-A 3 TGV PG11 bk	-	11			yes	6.5 - 12	10
19426000	H-A 3 TG M20 gr	20	-			-	-	10
19425500	H-A 3 TG M20 bk	20	-			-	-	10
19426400	H-A 3 TGV M20 gr	20	-			yes	3.0 - 13.5	10
19426700	H-A 3 TGV M20 bk	20	-			yes	3.0 - 13.5	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-A 3 TG



(24.04.2024)