

EPIC® MC module: HC2


The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

2 가


2



M



F



1

25mm²

ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 : ()

ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class : ()

(20.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® MC module: HC2

(V):	IEC: 1000 V
	UL: 600 V
	CSA: 600 V
(A):	82 A
:	3
:	< 2 mOhm
:	,
/ :	2
:	: 10 - 25 mm ²
(mm):	15
:	100
VDE- :	: VDE-REG. A870
	UL- :
	UL : E75770
:	-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .

(20.07.2024)



EPIC® MC module: HC2

	Article description	Contact type		Slots	Packaging unit
	:	2			
10344100	MCS-HC 2		2	2	5
10345100	MCB-HC 2		2	2	5

(20.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16