

EPIC® MH Gigabit Modul

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

EPIC® MH Gigabit Modul

10 GBit / s

가 , Cat. 7



Lapp



가 , 4 , Cat.7 Cu 가

10 Gbit/s(IEEE 802.3an)

1

Railway applications

- Fire protection on railway vehicles: Test according EN 45545-2. Requirement sets R22 and R23. Hazard level HL1, HL2 and HL3

Industry 4.0 applications

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® MH Gigabit Modul

/

ETIM 5:

(V):

:

(A):

:

:

/ :

:

:

VDE-

:

:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0

:

50

0,8 kV

5

3

UL94 V-0

8

PA

500

UL-

:

UL

: E75770

-40°C

+125°C

가

VAT

가

가

.

(23.04.2024)

©2024 Lapp Group - all rights reserved.



<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

	Article description	Contact type	Slots	/ PU
EPIC® MH Gigabit Kit				
44423291	EPIC® MHS Gigabit Kit small, AWG 24 - 28, cable diameter 5-7mm		1	1
44423292	EPIC® MHB Gigabit Kit small		1	1
44423326	EPIC® MHS Gigabit Kit medium		1	1
44423327	EPIC® MHB Gigabit Kit medium		1	1
EPIC® MH Gigabit Insulating body				
44423276	EPIC® MHS Gigabit		1	10
44423277	EPIC® MHB Gigabit		1	10
EPIC® MH Gigabit contact body metal				
44423278	EPIC® MHS Gigabit PIN		-	10
44423279	EPIC® MHS Gigabit PIN + GND		-	10
44423280	EPIC® MHB Gigabit PIN		-	10
44423281	EPIC® MHB Gigabit PIN + GND		-	10
EPIC® MH Gigabit cable clamp				
44423282	EPIC® MH Clamp 5 - 7 mm	-	-	10
44423283	EPIC® MH Clamp 7 - 10 mm	-	-	10
44423284	EPIC® MH Clamp 10 - 12 mm	-	-	10

EPIC® MH Gigabit Modul



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16