

HITRONIC® HDH -

LSZH ( ) 가 ( ); J-V (ZN) HH

12  
J-V(ZN)HH

CPR: www.lappkabel.com/cpr /



Ethernet



, , 가 ( )

3

: , , , , ,

12 (900 μm)

# HITRONIC® HDH -

LSZH  
 : OM3 (RAL 6027),  
 OM2 OM1 (RAL 2003)  
 가 : OS2( ) OM4( )

ETIM 5: ETIM 5.0 Class-ID: EC000034  
 ETIM 5.0 Class-Description:  
 ETIM 6: ETIM 6.0 Class-ID: EC000034  
 ETIM 6.0 Class : LWL  
 : (2 ): 900µm  
 :

Fibre type: GOF - Glass Optical Fibre  
 :: J-V(ZN)H  
 :  
 :  
 가 :  
 : 15 x  
 : 20 x  
 : -20 ~ 70°C

, 가 가 . ( . ) 가 .

가 VAT 가 가 .  
 OM4 가 .



HITRONIC® HDH

		Fibre type	Number of fibres	(mm)	(kg/km)
26010402	HITRONIC HDH 2G 50/125 OM4	50/125 OM4	2	6	34
26010404	HITRONIC HDH 4G 50/125 OM4	50/125 OM4	4	6.3	37
26010408	HITRONIC HDH 8G 50/125 OM4	50/125 OM4	8	7.5	57
26010412	HITRONIC HDH 12G 50/125 OM4	50/125 OM4	12	8.3	69
G 50 OM3					
26010302	HITRONIC® HDH 2G 50/125 OM3	50/125 OM3	2	6	34
26010304	HITRONIC® HDH 4G 50/125 OM3	50/125 OM3	4	6.3	37
26010308	HITRONIC® HDH 8G 50/125 OM3	50/125 OM3	8	7.5	57
26010312	HITRONIC® HDH 12G 50/125 OM3	50/125 OM3	12	8.3	69
G 50 OM2					
26010202	HITRONIC® HDH 2G 50/125 OM2	50/125 OM2	2	6	34
26010204	HITRONIC® HDH 4G 50/125 OM2	50/125 OM2	4	6.3	37
26010208	HITRONIC® HDH 8G 50/125 OM2	50/125 OM2	8	7.5	57
26010212	HITRONIC® HDH 12G 50/125 OM2	50/125 OM2	12	8.3	69
G 62.5 OM1					
26010102	HITRONIC® HDH 2G 62,5/125 OM1	62,5/125 OM1	2	6	34
26010104	HITRONIC® HDH 4G 62,5/125 OM1	62,5/125 OM1	4	6.3	37
26010108	HITRONIC® HDH 8G 62,5/125 OM1	62,5/125 OM1	8	7.5	57
26010112	HITRONIC® HDH 12G 62,5/125 OM1	62,5/125 OM1	12	8.3	69

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16