

EPIC® H-A 4

2.5 mm²

H-A

3



가

Made in Germany



M

F



Lapp



H-A 3 / H-A 4
H-A 3s

(20.07.2024)

EPIC® H-A 4

가

Railway applications

- Fire protection on railway vehicles: Test according EN 45545-2. Requirement sets R22 and R23. Hazard level HL1, HL2 and HL3

/

ETIM 5:	ETIM 5.0 Class-ID: EC000438
	ETIM 5.0 class :
ETIM 6:	ETIM 6.0 Class-ID: EC000438
	ETIM 5.0 class :
(V):	IEC: 400 V
	UL: 600 V
	CSA: 600 V
:	4 kV
(A):	IEC: 23 A
	UL: 10 A
	CSA: 10 A
:	3
:	UL94 V-0
:	1.5 - 4 mohm
:	,
/ :	4 + PE
:	: 0.5 - 2.5 mm ² (가 2.5 mm ²)
(mm):	6
:	100
VDE- :	: VDE-REG. : B437
	UL- :
	UL : E75770
:	-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .

(20.07.2024)



EPIC® H-A 4

	Article description	Contact type		Packaging unit
H-A 4				
10431000	H-A 4 SS		1 - 4	10
10432000	H-A 4 BS		1 - 4	10

(20.07.2024)



©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-A 4



(20.07.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16