

EPIC® MH 10.0mm

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

-



Lapp



Klauke D 22 HD 13
: 25, 35, 50, 70, 95mm²

(23.04.2024)



EPIC® MH 10.0mm

/

:

: 25mm² ... 95mm²

(mm):

23

:

brass silver plated CuZn / Ag

:

500

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® MH 10.0mm

	Article description	Contact type	(mm ²)	/ PU
EPIC® MH 10.0mm				
44423330	EPIC® MH SCEM AG 25sqmm D=10.0		25	10
44423331	EPIC® MH BCEM AG 25sqmm D=10.0		25	10
44423332	EPIC® MH SCEM AG 35sqmm D=10.0		35	10
44423333	EPIC® MH BCEM AG 35sqmm D=10.0		35	10
44423334	EPIC® MH SCEM AG 50sqmm D=10.0		50	10
44423335	EPIC® MH BCEM AG 50sqmm D=10.0		50	10
44423336	EPIC® MH SCEM AG 70sqmm D=10.0		70	10
44423337	EPIC® MH BCEM AG 70sqmm D=10.0		70	10
44423338	EPIC® MH SCEM AG 95sqmm D=10.0		95	10
44423339	EPIC® MH BCEM AG 95sqmm D=10.0		95	10

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16