

HITRONIC® TORSION

; PUR

2,4,8 12



Lapp



()

()

가 (, ,)

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

HITRONIC® TORSION

MIL-C-85045

2.5mm (LSZH)
(Aramid Yarns)

PUR
: (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000034

ETIM 5.0 Class-Description:

ETIM 6:

ETIM 6.0 Class-ID: EC000034

ETIM 6.0 Class : LWL

: : 2.5mm

Fibre type:

GOF - Glass Optical Fibre

::

A/J-V(ZN)H11Y

:

:

:

:

가 :

: 15 x

: 20 x

:

: -40°C

+70°C

: -30 °C ~ +70 °C

가

VAT
OM4

가

가 .
가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



HITRONIC® TORSION

		Fibre type	Number of fibres	(mm)	(kg/km)
Multimodale G50 OM4					
26310402	HITRONIC TORSION 2G 50/125 OM4	50/125 OM4	2	8.4	54
26310404	HITRONIC TORSION 4G 50/125 OM4	50/125 OM4	4	8.4	54
26310408	HITRONIC TORSION 8G 50/125 OM4	50/125 OM4	8	11.6	95
26310412	HITRONIC TORSION 12G 50/125 OM4	50/125 OM4	12	14.7	122
G 50 OM3					
26310302	HITRONIC® TORSION 2G 50/125 OM3	50/125 OM3	2	8.4	54
26310304	HITRONIC® TORSION 4G 50/125 OM3	50/125 OM3	4	8.4	54
26310308	HITRONIC® TORSION 8G 50/125 OM3	50/125 OM3	8	11.6	95
26310312	HITRONIC® TORSION 12G 50/125 OM3	50/125 OM3	12	14.7	122
G 50 OM2					
26310202	HITRONIC® TORSION 2G 50/125 OM2	50/125 OM2	2	8.4	54
26310204	HITRONIC® TORSION 4G 50/125 OM2	50/125 OM2	4	8.4	54
26310208	HITRONIC® TORSION 8G 50/125 OM2	50/125 OM2	8	11.6	95
26310212	HITRONIC® TORSION 12G 50/125 OM2	50/125 OM2	12	14.7	122
G 62.5 OM1					
26310102	HITRONIC® TORSION 2G 62,5/125 OM1	62,5/125 OM1	2	8.4	54
26310104	HITRONIC® TORSION 4G 62,5/125 OM1	62,5/125 OM1	4	8.4	54
26310108	HITRONIC® TORSION 8G 62,5/125 OM1	62,5/125 OM1	8	11.6	95
26310112	HITRONIC® TORSION 12G 62,5/125 OM1	62,5/125 OM1	12	14.7	122
E 9 OS2					
26310902	HITRONIC® TORSION 2E 9/125 OS2	9/125 OS2	2	8.4	54
26310904	HITRONIC® TORSION 4E 9/125 OS2	9/125 OS2	4	8.4	54

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



HITRONIC® TORSION

		Fibre type	Number of fibres	(mm)	(kg/km)
	9/125 OS2				
26310908	HITRONIC® TORSION 8E 9/125 OS2	9/125 OS2	8	11.6	95
26310912	HITRONIC® TORSION 12E 9/125 OS2	9/125 OS2	12	14.7	122

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16