

HITRONIC® HUW


가

HITRONIC® HUW , , , LSZH
J/A-DQ(ZN)(SR)H

CPR: www.lappkabel.com/cpr

가

(CST)가







(24.04.2024)

HITRONIC® HUW

24

LSZH
: (RAL 6018)

ETIM 5: ETIM 5.0 Class-ID: EC000034
ETIM 5.0 Class-Description:

ETIM 6: ETIM 6.0 Class-ID: EC000034
ETIM 6.0 Class : LWL

: 1 : 250µm
:

:

Fibre type: GOF - Glass Optical Fibre
:: A/J-DQ(ZN)(SR)H
: U-DQ(ZN)(SR)H

:

:

가 : : 15 x
: 20 x

가 : : 1500 N
: 2,000N

: : -30°C +70°C

, 가 가 . (.) 가 .

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



HITRONIC® HUW

OM4

가 .

(24.04.2024)



HITRONIC® HUW

		Fibre type	Number of fibres	(mm)	(kg/km)
G 50 OM4					
27500404	HITRONIC® HUW1500 4G 50/125 OM4	50/125 OM4	4	9.6	88
27500408	HITRONIC® HUW1500 8G 50/125 OM4	50/125 OM4	8	9.6	88
27500412	HITRONIC® HUW1500 12G 50/125 OM4	50/125 OM4	12	9.6	88
27500424	HITRONIC® HUW1500 24G 50/125 OM4	50/125 OM4	24	9.6	88
G 50 OM3					
27500304	HITRONIC® HUW1500 4G 50/125 OM3	50/125 OM3	4	9.6	88
27500308	HITRONIC® HUW1500 8G 50/125 OM3	50/125 OM3	8	9.6	88
27500312	HITRONIC® HUW1500 12G 50/125 OM3	50/125 OM3	12	9.6	88
27500324	HITRONIC® HUW1500 24G 50/125 OM3	50/125 OM3	24	9.6	88
G 50 OM2					
27500204	HITRONIC® HUW1500 4G 50/125 OM2	50/125 OM2	4	9.6	88
27500208	HITRONIC® HUW1500 8G 50/125 OM2	50/125 OM2	8	9.6	88
27500212	HITRONIC® HUW1500 12G 50/125 OM2	50/125 OM2	12	9.6	88
27500224	HITRONIC® HUW1500 24G 50/125 OM2	50/125 OM2	24	9.6	88
G 62.5 OM1					
27500104	HITRONIC® HUW1500 4G 62,5/125 OM1	62,5/125 OM1	4	9.6	88
27500108	HITRONIC® HUW1500 8G 62,5/125 OM1	62,5/125 OM1	8	9.6	88
27500112	HITRONIC® HUW1500 12G 62,5/125 OM1	62,5/125 OM1	12	9.6	88
27500124	HITRONIC® HUW1500 24G 62,5/125 OM1	62,5/125 OM1	24	9.6	88
E 9 OS2					

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



HITRONIC® HUW

		Fibre type	Number of fibres	(mm)	(kg/km)
27500904	HITRONIC® HUW1500 4E 9/125 OS2	9/125 OS2	4	9.6	88
27500908	HITRONIC® HUW1500 8E 9/125 OS2	9/125 OS2	8	9.6	88
27500912	HITRONIC® HUW1500 12E 9/125 OS2	9/125 OS2	12	9.6	88
27500924	HITRONIC® HUW1500 24E 9/125 OS2	9/125 OS2	24	9.6	88

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16