

HITRONIC® PCF DUPLEX FD

HITRONIC® PCF DUPLEX
A/J-V (ZN) H11Y 2K200/230

BUS PCF



500m

EMC

PROFIBUS, INTERBUS

HITRONIC® PCF DUPLEX FD

가 : 650nm, 850nm
BUS

FRNC : 2.2mm 가 PCF
(Aramid Yarns)
PUR : (RAL 2003)

ETIM 5:

ETIM 5.0 Class-ID: EC000034
ETIM 5.0 Class-Description:

ETIM 6:

ETIM 6.0 Class-ID: EC000034
ETIM 6.0 Class : LWL

:

Buffered fibre: 0.5mm
Single cable: 2.2 mm
Cable: 8.8mm

:

Fibre type:

PCF - K200/230
PCF - Polymer Cladded Fibre

:

: ≥ 15 x
: ≥ 20 x

::

A/J-V(ZN)H11Y

:

:

가 :

: 800N
: 2,000N

:

: -20 ~ +70 °C
: -10°C +50°C

, 가 가 . (.) 가 .

가 VAT 가 가 .

(24.04.2024)



HITRONIC® PCF DUPLEX FD

		Fibre type	Number of fibres	(mm)	(kg/km)
28320702	HITRONIC® PCF DUPLEX FD FRNC-PUR	200/230 PCF	2	8.8	63

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16