

# M1011

M1011



가



-



1

- "I"

M1011:

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# M1011

ETIM 5:

ETIM 5.0 Class-ID: EC000610

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000610

ETIM 6.0 Class :

:

: 2 mm

가 : A-Z, 2-9, -, .

:

: 4.7 mm

:

: 14.301 (EN ), SAE 304

: 0,12 mm

가

VAT

1

가

가

DYMO®

가



M1011

		(mm)	W (mm)	(m)	PU
61742670	M1011	4.7	-	-	1
61742710		-	12	4.8	1
61742720		-	12	3.65	1
61742700		-	12	6.4	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16