


# KMK Marking labels

KMK



10-31 mm

: , /

Smudge-proof: DIN 30646:1993-11,  
DIN VDE 0611-1:1977-11

: 150 (61742922) 50 (61742926) 10

: KMK: 5 mm  
KMK : 10-25 mm  
: KMK3: 10 mm  
KMK : 16-31 mm  
KMK2/KMK4: 5 mm

ETIM 5:

ETIM 5.0 Class-ID: EC001288  
ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001288  
ETIM 6.0 Class :

(24.04.2024)



# KMK Marking labels

:  
:  
:

Transparent  
- : PE,  
: , DIN A4 ,  
-40°C +80°C

가 VAT 가 가 .  
FLEXIMARK® . ) LCK 32 640 640 1 PU

(24.04.2024)



## KMK Marking Labels

		x (mm)		( )
61742820	KMK 1	29 x 8		100
61742822	KMK 2	29 x 8		100
61742824	KMK 3	40 x 17		50
61742826	KMK 4	40 x 17		50
61742922	ES/LP-BW-GB	29 x 8	-	10
61742926	ES/KMK 3GB	40 x 17	-	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16