

HITRONIC® POF SIMPLEX BUFFERED FIBRE

PE

HITRONIC® POF SIMPLEX PE, PE POF-Simplex , J-V2Y 1P 980/1000, 2.2mm,



70 m

EMC

,

PE (POF)

:

(24.04.2024)

HITRONIC® POF SIMPLEX BUFFERED FIBRE

ETIM 5:	ETIM 5.0 Class-ID: EC000034
	ETIM 5.0 Class-Description:
ETIM 6:	ETIM 6.0 Class-ID: EC000034
	ETIM 6.0 Class : LWL
:	: 2.2mm
Fibre type:	POF - P980/1000
::	J-V2Y
:	: PMMA
가 :	10 x
가 :	: 5 N
	- : 15 N
:	: -55 ~ +85°C
	: -10°C +50°C

가 VAT 가 가 . (.) 가 .



HITRONIC® POF SIMPLEX BUFFERED FIBRE

		Fibre type	Number of fibres	(mm)	(kg/km)
HITRONIC® POF SIMPLEX PE					
28000001	HITRONIC® POF SIMPLEX PE	980/1000 POF	1	2.2	3.8

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16