


# NYCY

, ; PVC ,  
 NYCY, VDE, PVC acc. HD603 / VDE 0276-603. , ,

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



PE

VDE HD 603/VDE 0276-603 - Part 3-G (point 4) 가 PVC  
 : 0.6m , 0.8m 가  
 PVC VDE standard HD 603/VDE 0276-603 - Part 3-G ( 4)  
 가 +70 °C

: IEC 60332-1-2  
 HD 603/VDE 0276-603, 3-G, 14 , ( HD 603/VDE 0276-603, Part 3-G, 5  
 +20 °C ) 15 ( HD 603/VDE 0276-603, Part 3-G, point 5 ,  
 가 +30 °C ) : VDE 0298-4, VDE 0298-4 , /  
 . ( T12 )

3 가 4 가 NYCWY 가 HD 603/VDE 0276-603  
 , 7 NYCY HD 627/VDE 0276-627

(24.04.2024)

# NYCY

:re, rm, se, sm :  
 r = ;  
 s = ;  
 e = ;  
 m = 가 ;  
 : PVC

PVC-

ETIM 5: ETIM 5.0 Class-ID: EC000057  
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000057  
ETIM 6.0 Class :

: 5 : VDE 0293-308 T9  
 6 :  
 : -  
 : : 12 x  
 : U0/U: 0.6/1.0 kV  
 : 4000 V  
 : : -5°C ~ +90°C  
 : : -40°C +70°C

, 가 가 . ( . ) 가 .  
 www.lappkabel.de/en/cable-standradlengths  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
15503003	2 x 1,5re/1,5	14	52	245
15503103	3 x 1,5re/1,5	14	66	280
15503203	4 x 1,5re/1,5	15	81	302
1550330	7 x 1,5re/2,5	17	133	450
1550332	12 x 1,5re/2,5	20	205	580
1550337	24 x 1,5re/6	26	413	1100
15503113	3 x 2,5re/2,5	15	104	316
15503213	4 x 2,5re/2,5	16	128	360
1550350	7 x 2,5re/2,5	18	200	530
1550355	16 x 2,5re/6	23	451	950
15503223	4 x 4re/4	18	200	485
15503233	4 x 6re/6	19	297	616
1550299	2 x 2,5re/2,5	12.6	80	241
15503123	3 x 4re/4	15.3	161	384
1550313	3 x 6re/6	16.7	240	484
1550322	7 x 4re/4	18.7	315	621

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16