


HITRONIC® HRH

가 ; J-V (ZN) HH

HITRONIC® HRH

J-V(ZN)HH, 가 OM1, OM2, OM3 oder OM4

CPR: www.lappkabel.com/cpr



Ethernet



가
()

3

:

(23.02.2024)



HITRONIC® HRH

		Fibre type	Number of fibres	(mm)	(kg/km)
G 50 OM4					
26000402	HITRONIC HRH400 2G 50/125 OM4	50/125 OM4	2	7	35
26000404	HITRONIC HRH600 4G 50/125 OM4	50/125 OM4	4	7	44
26000408	HITRONIC HRH1200 8G 50/125 OM4	50/125 OM4	8	9.7	77
26000412	HITRONIC HRH1700 12G 50/125 OM4	50/125 OM4	12	10.3	100
G 50 OM3					
26000302	HITRONIC® HRH400 2G 50/125 OM3	50/125 OM3	2	7	35
26000304	HITRONIC® HRH600 4G 50/125 OM3	50/125 OM3	4	7	44
26000308	HITRONIC® HRH1200 8G 50/125 OM3	50/125 OM3	8	9.7	77
26000312	HITRONIC® HRH1700 12G 50/125 OM3	50/125 OM3	12	10.3	100
G 50 OM2					
26000202	HITRONIC® HRH400 2G 50/125 OM2	50/125 OM2	2	7	35
26000204	HITRONIC® HRH600 4G 50/125 OM2	50/125 OM2	4	7	44
26000208	HITRONIC® HRH1200 8G 50/125 OM2	50/125 OM2	8	9.7	77
26000212	HITRONIC® HRH1700 12G 50/125 OM2	50/125 OM2	12	10.3	100
G 62.5 OM1					
26000102	HITRONIC® HRH400 2G 62,5/125 OM1	62,5/125 OM1	2	7	35
26000104	HITRONIC® HRH600 4G 62,5/125 OM1	62,5/125 OM1	4	7	44
26000108	HITRONIC® HRH1200 8G 62,5/125 OM1	62,5/125 OM1	8	9.7	77
26000112	HITRONIC® HRH1700 12G 62,5/125 OM1	62,5/125 OM1	12	10.3	100
E 9 OS2					
26000902	HITRONIC® HRH400 2E 9/125 OS2	9/125 OS2	2	7	35
26000904	HITRONIC® HRH600 4E	9/125 OS2	4	7	44

(23.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



HITRONIC® HRH

		Fibre type	Number of fibres	(mm)	(kg/km)
	9/125 OS2				
26000908	HITRONIC® HRH1200 8E 9/125 OS2	9/125 OS2	8	9.7	77
26000912	HITRONIC® HRH1700 12E 9/125 OS2	9/125 OS2	12	10.3	100

(23.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16