


NYY-J, NYY-O

PVC

NYY-J, NYY-O, VDE, PVC-Starkstromkabel nach HD603 / VDE 0276-603.

CPR: www.lappkabel.com/cpr

0,6/1,0 kV PVC NYM



VDE HD 603/VDE 0276-603 - Part 3-G (point 4) 가 PVC
 : 0.6m , 0.8m 가
 PVC VDE standard HD 603/VDE 0276-603 - Part 3-G (4)
 가 +70 °C

: IEC 60332-1-2
 HD 603/VDE 0276-603, 3-G, 14 , (HD 603/VDE 0276-603, Part 3-G, 5
 +20 °C) 15 (HD 603/VDE 0276-603, Part 3-G, point 5 , /
 가 +30 °C): VDE 0298-4, VDE 0298-4 ,
 . (T12)
 Maximum DC voltage to ground 1,8 kV according to HD 603 / DIN VDE 0276-603

HD 603/VDE 0276-603 (1 5)
 HD 627/VDE 0276-627 (7)

NYY-J, NYY-O

:re, rm, se, sm :
 r = ;
 s = ;
 e = ;
 m = 가 ;
 : PVC

PVC-

ETIM 5:	ETIM 5.0 Class-ID: EC000057	
	ETIM 5.0	
ETIM 6:	ETIM 6.0 Class-ID: EC000057	
	ETIM 6.0 Class :	
	5 : VDE 0293-308	T9
	6 :	
	- : 15 x	
	- : 12 x	
	U0/U: 0.6/1.0 kV	
	4000 V	
	J = GN/YE	
	O = GN/YE	
	: -5°C ~ +90°C	
	: -40°C +70°C	

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
NY-Y-J				
1550030	1 x 25rm	13	240	380
1550038	1 x 35rm	14	336	447
1550032	1 x 50rm	15	480	650
1550033	1 x 70rm	17	672	864
1550035	1 x 120rm	21.0	1152	1400
1550037	1 x 185rm	25	1776	2080
15500013	3 x 1,5re	12	43	223
15500023	4 x 1,5re	13	58	256
15500033	5 x 1,5re	14	72	293
1550004	7 x 1,5re	15	101	360
1550005	10 x 1,5re	18	144	520
1550006	12 x 1,5re	19	173	560
1550084	14 x 1,5re	20	202	620
1550007	16 x 1,5re	21	230	680
1550008	19 x 1,5re	22	274	760
1550009	24 x 1,5re	24	346	900
1550086	30 x 1,5re	26	432	1100
15500103	3 x 2,5re	13	72	272
15500113	4 x 2,5re	14	96	316
15500123	5 x 2,5re	15	120	323
1550013	7 x 2,5re	16	168	450
1550090	10 x 2,5re	20	240	630
1550091	12 x 2,5re	20	288	680
1550092	14 x 2,5re	21	336	790
1550094	19 x 2,5re	23	456	990
1550096	24 x 2,5re	26	576	1300
1550097	30 x 2,5re	28	720	1400
15500583	3 x 4re	15	115	373
15500203	4 x 4re	16	154	439
15500263	5 x 4re	17	192	510
15500593	3 x 6re	16	173	466
15500213	4 x 6re	17	230	547
15500273	5 x 6re	19	288	640

(12.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
15500603	3 x 10re	18	288	629
15500223	4 x 10re	19	384	743
15500823	5 x 10re	21	480	899
15500613	3 x 16re	20	461	850
15500233	4 x 16re	22	614	1039
15500833	5 x 16re	23	768	1240
15500713	3 x 25rm/16re	25	874	1595
15500243	4 x 25rm	27	960	1620
15500283	5x25rm	29.9	1200	1920
15500153	3 x 35sm/16re	27	1162	1718
15500753	4 x 35sm	27	1344	1916
15500163	3 x 50sm/25rm	31	1680	2383
15500253	4 x 50sm	31	1920	2639
1550104	5 x 50rm	36.8	2400	3325
15500173	3 x 70sm/35sm	33	2352	3196
15500763	4 x 70sm	35	2688	3576
1550105	5 x 70rm	40.6	3360	4465
15500183	3 x 95sm/50sm	38	3216	4271
15500773	4 x 95sm	40	3648	4746
15500723	3 x 120sm/70sm	41	4128	5281
15500783	4 x 120sm	43	4608	5813
15500733	3 x 150sm/70sm	46	4992	6408
15500793	4 x 150sm	48	5760	7263
15500743	3 x 185sm/95sm	50	6240	7909
15500803	4 x 185sm	53	7104	8905
15500193	3 x 240sm/120sm	57	8064	10162
15500813	4 x 240sm	60	9216	11430
NY-Y-O				
1550205	1 x 10re	10	96	176
1550206	1 x 16re	11	154	239
1550207	1 x 25rm	13	240	380
1550208	1 x 35rm	14	336	447
1550209	1 x 50rm	15	480	650
1550210	1 x 70rm	17	672	864

(12.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1550211	1 x 95rm	19	912	1132
1550212	1 x 120rm	21	1152	1405
1550213	1 x 150rm	22	1440	1710
1550214	1 x 185rm	25	1776	2080
1550215	1 x 240rm	27	2304	2669
1550216	1 x 300rm	30	2880	3305
1550218	1 x 500rm	39	4800	5400
15502003	2 x 1,5re	11	29	210
15502193	2 x 2,5re	12	48	250
15502203	2 x 4re	14	77	360
15502213	2 x 6re	15	115	400
15502223	2 x 10re	17	192	500
15502533	4 x 16re	22	614	1039
15502543	4 x 25rm	27	960	1620
15502563	4 x 50sm	31	1920	2639
15502573	4 x 70sm	35	2688	3576
15502583	4 x 95sm	40	3648	4746
15502503	4 x 4re	-	154	-

(12.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16