


HITRONIC® HDM

/ , 가

HITRONIC® HDM 4, 6 8 ,

A/J-V(ZN)11Y



, , 가 ()

TV

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

HITRONIC® HDM

MIL-C-85045

fibres

12

(900 μ m)

(Aramid Yarns)

PUR

: (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000034

ETIM 5.0 Class-Description:

ETIM 6:

ETIM 6.0 Class-ID: EC000034

ETIM 6.0 Class : LWL

:

(2) : 900μm

:

:

Fibre type:

GOF - Glass Optical Fibre

::

A/J-V(ZN)11Y

:

:

:

:

가 :

: 15 x

: 20 x

:

: -40°C +70°C

: -20°C +60°C

, 가 가 . (.) 가 .

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



HITRONIC® HDM

		Fibre type	Number of fibres	(mm)	(kg/km)
G 50 OM4					
26610404	HITRONIC® HDM600 4G 50/125 OM4	50/125 OM4	4	5.5	24
26610406	HITRONIC® HDM600 6G 50/125 OM4	50/125 OM4	6	5.6	29
26610408	HITRONIC® HDM700 8G 50/125 OM4	50/125 OM4	8	6.2	36
G 50 OM3					
26610304	HITRONIC® HDM600 4G 50/125 OM3	50/125 OM3	4	5.5	24
26610306	HITRONIC® HDM600 6G 50/125 OM3	50/125 OM3	6	5.6	29
26610308	HITRONIC® HDM700 8G 50/125 OM3	50/125 OM3	8	6.2	36
G 50 OM2					
26610204	HITRONIC® HDM600 4G 50/125 OM2	50/125 OM2	4	5.5	24
26610206	HITRONIC® HDM600 6G 50/125 OM2	50/125 OM2	6	5.6	29
26610208	HITRONIC® HDM700 8G 50/125 OM2	50/125 OM2	8	6.2	36
G 62.5 OM1					
26610104	HITRONIC® HDM600 4G 62.5/125 OM1	62,5/125 OM1	4	5.5	24
26610106	HITRONIC® HDM600 6G 62.5/125 OM1	62,5/125 OM1	6	5.6	29
26610108	HITRONIC® HDM700 8G 62.5/125 OM1	62,5/125 OM1	8	6.2	36
E 9 OS2					
26610904	HITRONIC® HDM600 4E9/125 OS2	9/125 OS2	4	5.5	24
26610906	HITRONIC® HDM600 6E9/125 OS2	9/125 OS2	6	5.6	29
26610908	HITRONIC® HDM700 8E9/125 OS2	9/125 OS2	8	6.2	36
26610912	HITRONIC® HDM700 12E9/125 OS2	9/125 OS2	12	6.7	49

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16