

N2XS2Y

PE ()

VDE 0276-620 N2XS2Y, VDE, PE (), ,

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV



EVU
 HD 620/VDE 0276-620 10-C (4)
 0.6m, 0.8m

가 :

PE
 HD 620/VDE 0276-620, 10-C, 7
 +20 °C)
 가 +30 °C) : VDE 0298-4, VDE 0298-4
 . (T12)

, (HD 620/VDE 0276-620, Part 10-C, 5
 8 (HD 620/VDE 0276-620, Part 10-C, point 5 ,
 , /

HD 620/ VDE 0276-620

(30.04.2024)

N2XS2Y

"rm": r = , m =
 : 가 (XLPE)

: PE,

ETIM 5:

ETIM 5.0 Class-ID: EC001140

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001140

ETIM 6.0 Class :

:

: 15 x

:

U_0/U : 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV

:

6/10 kV: 15 kV, 12/20 kV: 30 kV, 18/30

:

kV: 45 kV

:

: -40°C ~ +70°C

: -40°C ~ +90°C

 , 가 가 . (. .) 가 .
www.lappkabel.de/en/cable-standradlengths

가 VAT 가 가 .

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
6/10 (12) kV				
38107786	1x35 RM/16	24	518	770
38001000	1X50 RM/16	25	662	900
1552070	1X70 RM/16	26	854	1123
38107787	1x70 RM/50	27	1238	1450
38107788	1x95 RM/16	28	1094	1384
38107789	1x120 RM/16	30	1334	1623
38107029	1X150 RM/25	31	1723	1966
38107790	1x185 RM/25	33	2059	2335
1550067	1X240 RM/25	35	2587	2885
38107791	1x300 RM/25	37	3163	3480
38107792	1x400 RM/35	41	4234	4381
38107793	1x500 RM/35	43	5194	5382
12/20 (24) kV				
1552068	1X35 RM/16	28	518	914
1552069	1X50 RM/16	29	662	1049
1552041	1X70 RM/16	31	854	1289
3828017	1X95 RM/16	32	1094	1554
38107794	1x120 RM/16	34	1334	1802
1552047	1X150 RM/25	35	1723	2153
38107795	1x185 RM/25	37	2059	2533
38107796	1x240 RM/25	39	2587	3096
38107797	1x300 RM/25	42	3163	3705
38107798	1x300 RM/35	42	3274	3800
38107799	1x400 RM/35	44	4234	4519
38107800	1x500 RM/35	47	5194	5647
38107801	1x630 RM/35	51	6442	7049
18/30 (36) kV				
3036224	1X50 RM/16	34	662	1260
38107802	1x70 RM/16	36	854	1656
38107803	1x95 RM/16	37	1094	1789
38107804	1x120 RM/16	39	1334	2048
38107805	1x150 RM/25	40	1723	2409
3028167	1X185 RM/25	42	2059	2802



N2XS2Y

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
38107806	1x240 RM/25	44	2587	3382
38107807	1x300 RM/25	47	3163	4009
38107808	1x400 RM/35	50	4234	4934
38107809	1x500 RM/35	53	5194	6009
38107810	1x630 RM/35	56	6442	7423

(30.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16