


HITRONIC® HRM-FD Cable

가

Aufteilbares HITRONIC® HRM-FD

A/J-V(ZN)H(ZN)11Y flex

Highly flexible cable for power chain use







Lapp



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

HITRONIC® HRM-FD Cable

가 ()
가

MIL-C-85045
가

2.0mm
(LSZH)
(Aramid Yarns)

PUR
: (RAL 9005)

ETIM 5: ETIM 5.0 Class-ID: EC000034
ETIM 5.0 Class-Description:
ETIM 6: ETIM 6.0 Class-ID: EC000034
ETIM 6.0 Class : LWL
: : 2.0mm
:

Fibre type: GOF - Glass Optical Fibre
A/J-V(ZN)H(ZN)11Y
:
:
가 :
: 15 x
: 20 x
: -40°C +70°C
: -20°C +60°C

가 VAT 가 가 . (.) 가 .
가



HITRONIC® HRM-FD Cable

		Fibre type	Number of fibres	(mm)	(kg/km)
G 50 OM4					
26300402	HITRONIC® HRM-FD800 2G 50/125 OM4	50/125 OM4	2	7.8	50
26300404	HITRONIC® HRM-FD1000 4G 50/125 OM4	50/125 OM4	4	7.8	50
26300408	HITRONIC® HRM-FD1400 8G 50/125 OM4	50/125 OM4	8	10.4	93
26300412	HITRONIC® HRM-FD1800 12G 50/125 OM4	50/125 OM4	12	13	98
G 50 OM3					
26300302	HITRONIC® HRM-FD800 2G 50/125 OM3	50/125 OM3	2	7.8	50
26300304	HITRONIC® HRM-FD1000 4G 50/125 OM3	50/125 OM3	4	7.8	50
26300308	HITRONIC® HRM-FD1400 8G 50/125 OM3	50/125 OM3	8	10.4	93
26300312	HITRONIC® HRM-FD1800 12G 50/125 OM3	50/125 OM3	12	13	98
G 50 OM2					
26300202	HITRONIC® HRM-FD800 2G 50/125 OM2	50/125 OM2	2	7.8	50
26300204	HITRONIC® HRM-FD1000 4G 50/125 OM2	50/125 OM2	4	7.8	50
26300208	HITRONIC® HRM-FD1400 8G 50/125 OM2	50/125 OM2	8	10.4	93
26300212	HITRONIC® HRM-FD1800 12G 50/125 OM2	50/125 OM2	12	13	98
G 62.5 OM1					
26300102	HITRONIC® HRM-FD800 2G 62.5/125 OM1	62,5/125 OM1	2	7.8	50
26300104	HITRONIC® HRM-FD1000 4G 62.5/125 OM1	62,5/125 OM1	4	7.8	50
26300108	HITRONIC® HRM-FD1400 8G 62.5/125 OM1	62,5/125 OM1	8	10.4	93
26300112	HITRONIC® HRM-FD1800 12G 62.5/125 OM1	62,5/125 OM1	12	13	98
E 9 OS2					
26300902	HITRONIC® HRM-FD800 2E 9/125 OS2	9/125 OS2	2	7.8	50
26300904	HITRONIC® HRM-FD1000	9/125 OS2	4	7.8	50

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



HITRONIC® HRM-FD Cable

		Fibre type	Number of fibres	(mm)	(kg/km)
	4E 9/125 OS2				
26300908	HITRONIC® HRM-FD1400 8E 9/125 OS2	9/125 OS2	8	10.4	93
26300912	HITRONIC® HRM-FD1800 12E 9/125 OS2	9/125 OS2	12	13	98

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16