

NA2XS2Y

PE ()

VDE 0276-620 NA2XS2Y, VDE, PE (), ,

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
With aluminium conductor



EVU , ,
HD 620/VDE 0276-620 10-C (4) 가 :
0.6m, 0.8m

PE
HD 620/VDE 0276-620, 10-C, 7 , (HD 620/VDE 0276-620, Part 10-C, 5
+20 °C) 8 (HD 620/VDE 0276-620, Part 10-C, point 5 ,
가 +30 °C) : VDE 0298-4, VDE 0298-4 , /
. (T12)

HD 620/ VDE 0276-620

(24.04.2024)

NA2XS2Y

"rm": r = , m =
: 가 (XLPE)

: PE,

ETIM 5:

ETIM 5.0 Class-ID: EC001140

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001140

ETIM 6.0 Class :

:

:

:

:

:

: 15 x

U_0/U : 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV

6/10 kV: 15 kV, 12/20 kV: 30 kV, 18/30

kV: 45 kV

: -40°C ~ +70°C

: -40°C ~ +90°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
6/10 (12) kV				
38107886	1x50 RM/16	25	182	617
38107887	1x70 RM/16	26	182	701
38107888	1x95 RM/16	28	182	805
38107889	1x120 RM/16	30	182	900
32702886	1X150 RM/25	31	283	1081
38107890	1x185 RM/25	33	283	1215
32702885	1X240 RM/25	35	283	1414
38107891	1x300 RM/25	37	283	1614
38107892	1x400 RM/35	41	394	2022
38105313	1X500 RM/35	43	394	2367
38107893	1x630 RM/35	47	394	2815
12/20 (24) kV				
38107894	1x35 RM/16	28	182	700
32701312	1X50 RM/16	29	182	767
38107895	1x70 RM/16	31	182	860
38107896	1x70 RM/25	31	283	950
38000020	1X95 RM/16	32	182	974
1552075	1X120 RM/16	34	182	1078
30018695	1X150 RM/25	35	283	1267
38106595	1X185 RM/25	37	283	1412
38106519	1X240 RM/25	39	283	1625
38107897	1x300 RM/25	41	283	1839
3033789	1X400 RM/35	44	394	2224
38107898	1x500 RM/35	47	394	2597
1550993	1X630 RM/35	50	394	3281
1552072	1X800 RM/35	56	394	3983
18/30 (36) kV				
38107899	1x50 RM/16	34	182	980
38107900	1x70 RM/16	36	182	1083
38107901	1x95 RM/16	37	182	1209
38107902	1x120 RM/16	39	182	1324
38107903	1x150 RM/25	40	283	1522
38107904	1x185 RM/25	42	283	1680



NA2XS2Y

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
38107905	1x240 RM/25	44	283	1910
38107906	1x300 RM/25	46	283	2141
38107907	1x400 RM/35	49	394	2547
38107908	1x500 RM/35	52	394	2956
38107909	1x630 RM/35	56	394	3465

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16